


版 本	变 更 内 容	工程确认	日 期

备注:

1. 材质:
 - 1.1 胶芯: LCP+30%G.F UL94V-0
 - 1.2 端子: 高导电C7025/C2680; 镍底50U" MIN, 接触区域镀金 (AU 1u") 焊接区镀镀金G/F
 - 1.3 外壳: SUS201/SUS304, T=0.30mm (表面镀镍50U" MIN)
 - 1.4 中夹片: SUS304
2. 主要特性:
 - 2.1 额定电流: 3A/5A
 - 2.2 接触阻抗: 40mΩ MAX (初始值)
50mΩ MAX (测试后)
 - 2.3 绝缘阻抗: 100MΩ MIN
 - 2.4 耐压测试: 100V AC R.M.S.
 - 2.6 整体插入力: 5-20N 整体插入力: 5-20N (耐久后)
整体拔出力: 8-20N 整体拔出力: 6-20N (耐久后)
 - 2.7 耐久: 10000次
 - 2.8 耐高温: SMT回流焊 (峰值260° ±5°), 塑胶不能有起泡, 融胶等不良, 变色, 翘曲变形在公差范围以内
 - 2.9 产品须做焊锡测试, 粘锡面积达到95%以上
 - 3.0 盐雾测试: 24H MIN/48H MIN
 - 3.1 工作温度: -30℃~+85℃



PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

yiYUAN 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD 品名 (ITEM NO) Type C 母座16P 立贴H=6.5 (脚长0.95) 料号 (PART NO) YTC-TC16-565 图号 (DWG NO)		页码 (SHEET)	1/1	单位(UNIT): MM
		版本 (REV)	A1	比例(SCALE)
		日期 (DATE)	2021.10.12	未注公差 TOLERANCE UNSPECIFIED X.X ±0.15 X.XX ±0.05 X.XXX ±0.02 X° ±5° X.X° ±2°
		设计 (DESIGN)	LUO	
		审核 (CHECKED)	ROGER LI	
		核准 (APPROVED)	ROC ZHAO	
These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way				