

TO-252 Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=20V$
- $I_D=60A$
- $R_{DS(on)}@V_{GS}=4.5V < 7m\Omega$
- $R_{DS(on)}@V_{GS}=2.5V < 9m\Omega$
- Avalanche energy tested
- Fast Switching Speedze
- Improved dv/dt capability, high ruggedness


Applications

- DC-DC Converter
- Ideal for high-frequency switching and synchronous rectification

Mechanical Data

- Case: TO-252
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Drain-source Voltage
20 V
Drain Current
60 Ampere



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
TO-252	R3	0.305	2500	5000	40000	13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	20
Gate-source Voltage	V_{GS}	V	± 12
Drain Current	I_D	A	60
Pulsed Drain Current ⁽¹⁾	I_{DM}	A	240
Total Power Dissipation	P_D	W	37
Single pulse avalanche energy ⁽²⁾	EAS	mJ	36
Junction temperature	T_J	°C	-55 ~+150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	°C / W	3.4

● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =250μA	V	20	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =20V, V _{GS} =0V	μA	—	—	1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±12V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =250μA	V	0.5	0.75	1.0
Static Drain-Source On-Resistance ⁽³⁾	R _{DS(ON)}	V _{GS} = 4.5V, I _D =30A	mΩ	—	4.8	7
		V _{GS} = 2.5V, I _D =10A		—	6	9

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =10V, V _{GS} =0V, f=1MHZ	pF	—	1980	—
Output Capacitance	C _{oss}			—	305	—
Reverse Transfer Capacitance	C _{rss}			—	295	—

● Switching Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =4.5V, V _{DD} =10V, I _D =20A, R _{GEN} =3Ω	nS	—	11	—
Turn-on Rise Time	t _r		nS	—	33	—
Turn-off Delay Time	t _{D(off)}		nS	—	47	—
Turn-off fall Time	t _f		nS	—	95	—
Total Gate Charge	Q _g	V _{DS} =10V, I _D =20A V _{GS} =4.5V	nC	—	27	—
Gate-Source Charge	Q _{gs}		nC	—	6.5	—
Gate-Drain Charge	Q _{gd}		nC	—	6.4	—

● Drian-Source Diode Characteristics

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =60A, V _{GS} =0V	V	—	—	1.2
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	60
Reverse Recovery Time	V _{rr}	I _S =60A, di/dt=100A/us, TJ=25°C	nS	—	11	—
Reverse Recovery Charge	Q _{rr}		nC	—	3	—







Note:

(1) Repetitive Rating: Pulse width limited by maximum junction temperature.






(2) EAS condition : Tj=25°C ,VDD=10V,VG=10V,L=0.5mH,IAS=12A,Rg=25Ω.

(3) Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Package Outline Dimensions (TO-252)



● Suggested Pad Layout




1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

