

IDEAS GENERATED DRAWING, DO NOT CHANGE BY HAND

REV.	ECN. NO.	APPD.
A	BC-10-0131689	Herry Yang
B	BC-11-0001491	Herry Yang
C	BC-11-0060226	Herry Yang
D	BC-12-0008691	Y.H.Mao




NOTES:


- ELECTRICAL CHARACTERISTICS:
 - CONTACT CURRENT RATING: 0.5 AMPERE MAX. PER PIN.
(PER PIN) DOESN'T EXCEED 30°C ABOVE AMBIENT AT 0.5 AMPERE MAX. PER PIN.
 - VOLTAGE RATING: 50V AC.
 - INSULATION RESISTANCE: 500 MEGAOHMS MIN. AT 500V DC.
 - DIELECTRIC WITHSTANDING VOLTAGE: 300V AC RMS AT 60Hz, FOR 1 MINUTE.
 - CONTACT RESISTANCE : 55 MILLIOHMS MAX. PER PIN INITIAL.
 $\Delta R=20$ MILLIOHMS MAX. PER PIN AFTER FULL ENVIRONMENTAL TESTING.
- MECHANICAL CHARACTERISTICS: DURABILITY: 50 MATING CYCLES.
- OPERATION TEMPERATURE: -40°C TO +80°C.
- PLEASE CONTACT FOXCONN SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS & AVAILABILITY.


PART NO. DESCRIPTION: A S 0 B2 2 * - S 52 * - 7 H

MEMORY MODULE SOCKET
HORIZONTAL TYPE
SINGLE ROW
NO. OF POS.
B2= 52 POS.
SMT
CONTACT AREA PLATING
6=10u" GOLD PLATING
1=GOLD FLASH

H=HALOGEN/LEAD FREE
7=TAPE&REEL
Q=GENERAL TYPE
K=ONLY CLIP
52=5.2mm HEIGHT
STANDARD TYPE




X. ± 0.30	X°. ± 2°	UNITS mm	NAME (INTENDED USE)	FOXCONN HON HAI PRECISION IND. CO., LTD. TAIPEI, TAIWAN, R.O.C.			
.X ± 0.25	.X°. ± 1°		MINI PCI EXPRESS CONNECTOR				
.XX ± 0.15	.XX°. ±	MAT'L	PART NO. (INTENDED USE)	TITLE: CUSTOMER DRAWING			
.XXX ±	.XXX°. ±		AS0B22*-S52*-7H				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.		FINISH	APPD: Y.H.Mao	DWG NO.: 317-0000-2008			
		Q'TY	CHKD: ZH.Wang				
				DR: Li Ping Yang 2/7'12		SCALE	SHEET
						N/A	1/7





⑥	CAP	1	THERMOPLASTIC	UL94V-0, IVORY COLOR(IN ORDER TO PICK-UP,TAKE AWAY AFTER ASSEMBLY)
⑤	CLIP(2)	1	STAINLESS STEEL	2u" Pd PLATING OVER SOLDER PAD AREA
④	CLIP(1)	1	STAINLESS STEEL	NO PLATING
③	BOARD LOCK	2	COPPER ALLOY	100u" MATTE TIN PLATING OVER ALL
②	CONTACT	52	COPPER ALLOY	50u" NICKEL UNDER PLATING GOLD FLASH AT TAIL 10u" GOLD PLATING OR GOLD FLASH AT CONTACT AREA
①	HOUSING	1	THERMOPLASTIC	UL94V-0, IVORY COLOR


ITEM	DESCRIPTION	Q'TY	MATERIAL	TREATMENT		
X.±	0.30	X°±	UNITS	mm	NAME(INTENDED USE)	FOXCONN HON HAI PRECISION IND. CO.,LTD. TAIPEI, TAIWAN, R.O.C.
.X±	0.25	.X°±	MAT'L		MINI PCI EXPRESS CONNECTOR	
.XX±	0.15	.XX°±			PART NO.(INTENDED USE)	TITLE:
.XXX±		.XXX°±	FINISH		AS0B22*-S52*-7H	CUSTOMER DRAWING
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.					APPD: Y.H.Mao	DWG NO.: 317-0000-2008
					CHKD: Alex Wong	
					DR: LiPing Yang 2/7'12	




SCALE	SHEET	REV.
N/A	2/7	D











IDEAS GENERATED DRAWING, DO NOT CHANGE BY HAND

REV.	ECN.	NO.	APPD.




NOTES:

1. 10 POCKETS HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.20\text{mm}$.
2. COVER TAPE PEELING STRENGTH : 0.01 kgf MIN & 0.13 kgf MAX. AT 300mm/min.



3. PACKING CAPACITY :

PART No.	PCS / REEL	REEL / BOX	PCS / BOX
ASOB22*-S52Q-7H	500	5	2500
ASOB22*-S52K-7H	500	5	2500

X. ± 0.30	X° ±	UNITS mm	NAME (INTENDED USE)	FOXCONN HON HAI PRECISION IND. CO.,LTD. TAIPEI, TAIWAN, R.O.C.			
.X ± 0.25	.X° ±		MAT'L				
.XX ± 0.15	.XX° ±	FINISH	PART NO. (INTENDED USE)	TITLE:			
.XXX ±	.XXX° ±		ASOB22*-S52*-7H	CUSTOMER DRAWING			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.			APPD: Y.H.Mao	DWG NO.: 317-0000-2008			
		Q'TY	CHKD: Alex Wong				
			DR: LiPing Yang 2/8'12				