

P-Channel Enhancement Mode Power MOSFET

Description


The GT1K3P20D5 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge. It can be used in a wide variety of applications.

General Features


- V_{DS} -200V
- I_D (at $V_{GS} = -10V$) -25A
- $R_{DS(ON)}$ (at $V_{GS} = -10V$) < 125m Ω
- 100% Avalanche Tested
- RoHS Compliant

Application


- Power switch
- DC/DC converters



Schematic diagram



pin assignment



DFN5X6-8L

Ordering Information

Device	Package	Marking	Packaging
GT1K3P20D5	DFN5X6-8L	GT1K3P20	5000pcs/Reel

Absolute Maximum Ratings $T_C = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-200	V
Continuous Drain Current	I_D	$T_C = 25^\circ\text{C}$	A
		$T_C = 100^\circ\text{C}$	
Pulsed Drain Current (note1)	I_{DM}	-100	A
Gate-Source Voltage	V_{GS}	± 20	V
Power Dissipation	P_D	160	W
Single pulse avalanche energy (note2)	E_{AS}	240	mJ
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 To 150	$^\circ\text{C}$

Thermal Resistance

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Ambient	R_{thJA}	50	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Case	R_{thJC}	0.78	$^\circ\text{C/W}$

Specifications T _J = 25°C, unless otherwise noted						
Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Parameters						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = -250μA	-200	--	--	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = -200V, V _{GS} = 0V	--	--	-1	μA
Gate-Source Leakage	I _{GSS}	V _{GS} = ±20V	--	--	±100	nA
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = -250μA	-2.0	-3.5	-4.0	V
Drain-Source On-Resistance	R _{DS(on)}	V _{GS} = -10V, I _D = -15A	--	99	125	mΩ
Forward Transconductance	g _{FS}	V _{DS} = -5V,I _D = -15A	--	15	--	S
Dynamic Parameters						
Input Capacitance	C _{iss}	V _{GS} = 0V, V _{DS} = -100V, f = 0.8MHz	--	4050	--	pF
Output Capacitance	C _{oss}		--	150	--	
Reverse Transfer Capacitance	C _{rss}		--	5	--	
Total Gate Charge	Q _g	V _{DD} = -100V, I _D = -15A, V _{GS} = -10V	--	138	--	nC
Gate-Source Charge	Q _{gs}		--	36	--	
Gate-Drain Charge	Q _{gd}		--	68	--	
Turn-on Delay Time	t _{d(on)}	V _{DD} = -100V, I _D = -15A, R _G = 1.6Ω	--	32	--	ns
Turn-on Rise Time	t _r		--	29	--	
Turn-off Delay Time	t _{d(off)}		--	57	--	
Turn-off Fall Time	t _f		--	22	--	
Drain-Source Body Diode Characteristics						
Continuous Body Diode Current	I _S	T _C = 25°C	--	--	-25	A
Body Diode Voltage	V _{SD}	T _J = 25°C, I _{SD} = -15A, V _{GS} = 0V	--	--	-1.2	V
Reverse Recovery Charge	Q _{rr}	I _F = -15A, V _{GS} = 0V di/dt=-100A/us	--	320	--	nC
Reverse Recovery Time	T _{rr}		--	170	--	ns

Notes


1. Repetitive Rating: Pulse width limited by maximum junction temperature

2. EAS condition : $T_J = 25^{\circ}\text{C}$, $V_{DD} = 50V$, $V_{GS} = 10V$, $L = 0.5mH$, $R_G = 25\Omega$


The table shows the minimum avalanche energy, which is 650mJ when the device is tested until failure

3. Identical low side and high side switch with identical R_G


Gate Charge Test Circuit



Switch Time Test Circuit



EAS Test Circuit



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Drain Source On Resistance




Figure 4. Gate Charge




Figure 5. Capacitance





Figure 6. Source-Drain Diode Forward



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Drain-Source On-Resistance




Figure 8. Safe Operation Area




Figure 9. Maximum Continuous Drain Current vs Case Temperature






Figure 10. Normalized Maximum Transient Thermal Impedance



DFN5X6-8L Package Information



DIM. SYMBOL	MILLIMETERS		
	MIN.	NOM.	MAX.
A	1.00	1.10	1.20
A1	0	---	0.05
b	0.30	0.40	0.50
c	0.20	0.25	0.30
D1	5.10	5.20	5.30
D2	3.90	4.10	4.25
E	6.00	6.15	6.30
E1	5.76	5.86	5.96
E2	3.52	3.72	3.92
e	1.27 BSC		
H	0.40	0.50	0.60
L	0.50	0.61	0.71
L1	0.05	0.15	0.25
L2	0.02	0.08	0.15
K	1.10	---	---