



深圳市兴华鑫电子科技有限公司  
Shenzhen xinghuaxin Electronic Technology Co., Ltd

# 承認書

## SPECIFICATION FOR APPROVAL

客戶(Customer): \_\_\_\_\_  
客戶料號(Customer P/N): \_\_\_\_\_  
興華鑫型號(Supplier P/N): 3610-DC12V-L100MM  
產品名稱(Description): 蜂鸣器 (Buzzer)  
產品規格(Specification): 36\*31MM 有源压电式

|                                                |                                        |     |     |
|------------------------------------------------|----------------------------------------|-----|-----|
| 客戶承認欄<br>(Customer Authorization<br>Signature) | 深圳市興華鑫電子科技有限公司 承認欄<br>(Supplier Audit) |     |     |
|                                                | 審核                                     | 檢查  | 制作  |
|                                                | 唐国兴                                    | 唐玉来 | 吴银娟 |
|                                                | 日期: 2022 年 04 月 19 日<br>版次: A          |     |     |


声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路88号厂房四层  
TEL: 0755-27892904  
E-mail: jacky.tang@jsxhxdz.com  
Http: [www.jsxhxdz.com](http://www.jsxhxdz.com)

1.SPECIFICATION 规格

| No. | Item                                | Unit | Specification | Condition                |
|-----|-------------------------------------|------|---------------|--------------------------|
| 1   | Oscillation Frequency               | Hz   | 3000±500      |                          |
| 2   | Operating Voltage                   | VDC  | 3 ~ 26        |                          |
| 3   | Rated Voltage                       | VDC  | 12            |                          |
| 4   | Current Consumption                 | mA   | MAX. 10       | at Rated Voltage         |
| 5   | Sound Pressure Level                | dB   | MIN. 100      | at 10cm at Rated Voltage |
| 6   | Operating Temperature               | ℃    | -20 ~ +70     |                          |
| 7   | Storage Temperature                 | ℃    | -30 ~ +85     |                          |
| 8   | Dimension                           | mm   | Φ43x H33      | See appearance drawing   |
| 9   | Weight (MAX)                        | gram | 40            |                          |
| 10  | Housing Material                    |      | ABS( Black )  |                          |
| 11  | Leading Pin                         |      | Sn            | See appearance drawing   |
| 12  | Environmental Protection Regulation |      | RoHS          |                          |

2.APPEARANCE DRAWING 尺寸图




### 3. TESTING METHOD 測量方式

#### Standard Measurement conditions


Temperature:  $25 \pm 2^\circ\text{C}$  Humidity: 45-65%

#### Acoustic Characteristics:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below




In the measuring test, buzzer is placed as follows:



### 4. VOLTAGE / CURRENT / SOUND PRESSURE CHARACTERISTICS



## 5. RELIABILITY TEST 可靠性测试

| NO. | ITEM                            | TEST CONDITION AND REQUIREMENT                                                                                                                                                                                        |
|-----|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1   | High Temperature Test (Storage) | After being placed in a chamber with 80 °C for 96hours and then being placed in normal condition for 2hours.<br>Allowable variation ofSPL after test: 10dB.                                                           |
| 2   | Low Temperature Test (Storage)  | After being Placed in a chamber with-30 °C for 96hours and then being placed in normal condition for 2hours.<br>Allowable variation ofSPL after test: 10dB.                                                           |
| 3   | Humidity Test                   | After being Placed in a chamber with 90-95% R.H. at 40 °C for 96 hours and then being placed in normal condition for 2hours.<br>Allowable variation ofSPL after test: 10dB.                                           |
| 4   | Temperature Cycle Test          | <p>The part shall be subjected to 5 cycles. One cycle shall be consist of:</p>  <p>Allowable variation ofSPL after test: 10dB.</p> |
| 5   | Drop Test                       | Drop on a hardwood board of4cm thick, anydirections ,6 times, at the height of75cm .<br>Allowable variation ofSPL after test: 10dB.                                                                                   |
| 6   | Vibration Test                  | After being applied vibration ofamplitude of 1.5mm with 10 to 55 Hz band ofvibration frequency to each of3 perpendicular directions for 2 hours .<br>Allowable variation ofSPL after test: 10dB.                      |
| 7   | Solderability Test              | Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of+300 °C for 3 1 seconds .<br>90% min. lead terminals shall be wet with solder (Except the edge ofterminals).                    |
| 8   | Terminal Strength Pulling Test  | The force of9.8N(1.0kg) is applied to each terminal in axial direction for 10 seconds.<br>No visible damage and cutting of.                                                                                           |

### TEST CONDITION.

|                         |   |                             |                      |                            |
|-------------------------|---|-----------------------------|----------------------|----------------------------|
| Standard Test Condition | : | a) Temperature : +5 ~ +35°C | b) Humidity : 45-85% | c) Pressure : 860-1060mbar |
| 一般测试条件                  | : | a) 温度 : +5 ~ +35°C          | b) 湿度 : 45-85%       | c) 气压 : 860-1060mbar       |
| Judgment Test Condition | : | a) Temperature : +25 ± 2°C  | b) Humidity : 60-70% | c) Pressure : 860-1060mbar |
| 争议时测试条件                 | : | a) 温度 : +25 ± 2°C           | b) 湿度 : 60-70%       | c) 气压 : 860-1060mbar       |