

## Description

The HSU6032A is the high cell density trench N-ch MOSFETs, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.


The HSU6032A meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

- Super Low Gate Charge
- 100% EAS Guaranteed
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench technology

## Product Summary

|                  |     |    |
|------------------|-----|----|
| $V_{DS}$         | 60  | V  |
| $R_{DS(ON),typ}$ | 6.7 | mΩ |
| $I_D$            | 75  | A  |

## TO-252 Pin Configuration



## Absolute Maximum Ratings

| Symbol                 | Parameter                                  | Rating     | Units       |
|------------------------|--------------------------------------------|------------|-------------|
| $V_{DS}$               | Drain-Source Voltage                       | 60         | V           |
| $V_{GS}$               | Gate-Source Voltage                        | $\pm 20$   | V           |
| $I_D@T_C=25^{\circ}C$  | Continuous Drain Current, $V_{GS} @ 10V^1$ | 75         | A           |
| $I_D@T_C=100^{\circ}C$ | Continuous Drain Current, $V_{GS} @ 10V^1$ | 52         | A           |
| $I_{DM}$               | Pulsed Drain Current <sup>2</sup>          | 300        | A           |
| EAS                    | Single Pulse Avalanche Energy <sup>3</sup> | 280        | mJ          |
| $P_D@T_C=25^{\circ}C$  | Total Power Dissipation <sup>4</sup>       | 100        | W           |
| $T_{STG}$              | Storage Temperature Range                  | -55 to 150 | $^{\circ}C$ |
| $T_J$                  | Operating Junction Temperature Range       | -55 to 150 | $^{\circ}C$ |

## Thermal Data

| Symbol          | Parameter                                        | Typ. | Max. | Unit          |
|-----------------|--------------------------------------------------|------|------|---------------|
| $R_{\theta JA}$ | Thermal Resistance Junction-ambient <sup>1</sup> | ---  | 62   | $^{\circ}C/W$ |
| $R_{\theta JC}$ | Thermal Resistance Junction-case <sup>1</sup>    | ---  | 1.3  | $^{\circ}C/W$ |

**Electrical Characteristics ( $T_J=25^\circ\text{C}$ , unless otherwise noted)**

| Symbol       | Parameter                                      | Conditions                                                   | Min. | Typ. | Max.      | Unit       |
|--------------|------------------------------------------------|--------------------------------------------------------------|------|------|-----------|------------|
| $BV_{DSS}$   | Drain-Source Breakdown Voltage                 | $V_{GS}=0V$ , $I_D=250\mu A$                                 | 60   | ---  | ---       | V          |
| $R_{DS(ON)}$ | Static Drain-Source On-Resistance <sup>2</sup> | $V_{GS}=10V$ , $I_D=20A$                                     | ---  | 6.7  | 8.4       | m $\Omega$ |
| $V_{GS(th)}$ | Gate Threshold Voltage                         | $V_{GS}=V_{DS}$ , $I_D=250\mu A$                             | 2    | ---  | 4         | V          |
| $I_{DSS}$    | Drain-Source Leakage Current                   | $V_{DS}=48V$ , $V_{GS}=0V$ , $T_J=25^\circ\text{C}$          | ---  | ---  | 1         | $\mu A$    |
|              |                                                | $V_{DS}=48V$ , $V_{GS}=0V$ , $T_J=55^\circ\text{C}$          | ---  | ---  | 5         |            |
| $I_{GSS}$    | Gate-Source Leakage Current                    | $V_{GS}=\pm 20V$ , $V_{DS}=0V$                               | ---  | ---  | $\pm 100$ | nA         |
| $R_g$        | Gate Resistance                                | $V_{DS}=0V$ , $V_{GS}=0V$ , $f=1\text{MHz}$                  | ---  | 1.72 | ---       | $\Omega$   |
| $Q_g$        | Total Gate Charge (10V)                        | $V_{DS}=30V$ , $V_{GS}=10V$ , $I_D=40A$                      | ---  | 61   | ---       | nC         |
| $Q_{gs}$     | Gate-Source Charge                             |                                                              | ---  | 17   | ---       |            |
| $Q_{gd}$     | Gate-Drain Charge                              |                                                              | ---  | 24   | ---       |            |
| $T_{d(on)}$  | Turn-On Delay Time                             | $V_{DD}=30V$ , $V_{GS}=10V$ , $R_G=3.3\Omega$ ,<br>$I_D=20A$ | ---  | 16.2 | ---       | ns         |
| $T_r$        | Rise Time                                      |                                                              | ---  | 29.2 | ---       |            |
| $T_{d(off)}$ | Turn-Off Delay Time                            |                                                              | ---  | 36.4 | ---       |            |
| $T_f$        | Fall Time                                      |                                                              | ---  | 2.2  | ---       |            |
| $C_{iss}$    | Input Capacitance                              | $V_{DS}=30V$ , $V_{GS}=0V$ , $f=1\text{MHz}$                 | ---  | 3207 | ---       | pF         |
| $C_{oss}$    | Output Capacitance                             |                                                              | ---  | 211  | ---       |            |
| $C_{rss}$    | Reverse Transfer Capacitance                   |                                                              | ---  | 181  | ---       |            |


**Diode Characteristics**

| Symbol   | Parameter                                | Conditions                                                 | Min. | Typ. | Max. | Unit |
|----------|------------------------------------------|------------------------------------------------------------|------|------|------|------|
| $I_S$    | Continuous Source Current <sup>1,5</sup> | $V_G=V_D=0V$ , Force Current                               | ---  | ---  | 75   | A    |
| $V_{SD}$ | Diode Forward Voltage <sup>2</sup>       | $V_{GS}=0V$ , $I_S=1A$ , $T_J=25^\circ\text{C}$            | ---  | ---  | 1.2  | V    |
| $t_{rr}$ | Reverse Recovery Time                    | $I_F=20A$ , $dI/dt=100A/\mu s$ ,<br>$T_J=25^\circ\text{C}$ | ---  | 72   | ---  | nS   |
| $Q_{rr}$ | Reverse Recovery Charge                  |                                                            | ---  | 42   | ---  | nC   |


Note :

- 1.The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width  $\leq 300\mu s$  , duty cycle  $\leq 2\%$
- 3.The EAS data shows Max. rating . The test condition is  $V_{DD}=40V$ ,  $V_{GS}=10V$ ,  $L=0.5mH$
- 4.The power dissipation is limited by  $150^\circ\text{C}$  junction temperature
- 5.The data is theoretically the same as  $I_D$  and  $I_{DM}$  , in real applications , should be limited by total power dissipation.


### Typical Characteristics




**Figure 7. Gate Charge Waveforms**




**Figure 8. Capacitance**




**Figure 9. Body-Diode Characteristics**



**Figure 10. Maximum Safe Operating Area**



# TO252-2L Package Outline



| SYMBOLS  | MILLIMETERS |      | INCHES   |       |
|----------|-------------|------|----------|-------|
|          | MIN         | MAX  | MIN      | MAX   |
| A        | 2.18        | 2.40 | 0.086    | 0.095 |
| A1       | -           | 0.2  | -        | 0.008 |
| b        | 0.68        | 0.9  | 0.026    | 0.036 |
| b3       | 4.95        | 5.46 | 0.194    | 0.215 |
| c        | 0.43        | 0.89 | 0.017    | 0.035 |
| D        | 5.97        | 6.22 | 0.235    | 0.245 |
| D1       | 5.300REF    |      | 0.209REF |       |
| E        | 6.35        | 6.73 | 0.250    | 0.265 |
| E1       | 4.32        | --   | 0.170    | -     |
| e        | 2.286BSC    |      | 0.09BSC  |       |
| H        | 9.4         | 10.5 | 0.370    | 0.413 |
| L        | 1.38        | 1.78 | 0.054    | 0.070 |
| L1       | 2.90REF     |      | 0.114REF |       |
| L2       | 0.51BSC     |      | 0.020BSC |       |
| L3       | 0.88        | 1.28 | 0.034    | 0.050 |
| L4       | 0.5         | 1    | 0.019    | 0.039 |
| $\theta$ | 0°          | 8°   | 0°       | 8°    |