



汇隆电子(金华)有限公司
HUILONG ELECTRONIC (JINHUA) CO.,LTD

SPECIFICATION FOR APPROVAL

CUSTOMER

NOMINAL FREQUENCY

38.400000 MHz

HOLDER TYPE

3225

SPEC. NO. (P/N)

HL38400020

CUSTOMER P/N

ISSUE DATE

Apr.2,2020

APPROVED	PREPARED	QA
		
APPROVED BY CUSTOMER :		AVL Status
Please return one copy with approval to HLC		

浙江省金华市经济开发区工业园区秋涛北街399号
No.399 Qiutao North Str., Industrial Area, Economic
Development Zone, Jinhua, Zhejiang, China
TEL: 0086-579-82273331
FAX: 0086-579-82273198
<http://www.cn-hlc.com>



RoHS Compliant (Pb- Free)



TYPE HL SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HL38400020

Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	38.400000			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	LC	10			pF	
Frequency Tolerance	FT	± 10			ppm	at 25°C $\pm 3^{\circ}\text{C}$
Frequency Stability		± 25			ppm	with working temperature Reference to 25°C
Working temperature range	TR	-20~95			°C	
Drive Level	DL	100			μW	Max.
Series Resonant Resistance RF	CI/RR	30			Ω	Max.
Insulation Resistance	IR	>500			M Ω	
Shunt Capacitance C0	C0		0.8	2	pF	
Aging		3			ppm/yr.	
Storage temperature range		-55 ~ 125			°C	
Unit Weight					g	

HUILONG ELECTRONIC (JINHUA) CO.,LTD

H0-R-4-014



TYPE HL SEAM SEALED X'TAL

MARKING

HLC

*38.4xx

HLC: HLC Use Code x: CL Code

x: Date Code

CL	Code	CL	Code	CL	Code
0pf	0	7.5pf	H	11.2pf	a
6pf	1	11pf	I	11.4pf	b
8pf	2	8.5pf	J	13.5pf	d
10pf	3	7.1pf	K	20.5pf	e
12pf	5	19pf	L	8.8pf	f
15pf	6	12.5p	M	17pf	g
16pf	7	27pf	N	4.3pf	h
18pf	8	7.3pf	O		
20pf	9	13pf	P		
22pf	A	11.5p	Q		
25pf	B	7pf	R		
28pf	C	14pf	S		
30pf	D	23pf	T		
32pf	E	11.1p	U		
9.5pf	F	33pf	V		
9pf	G	10.5p	W		
		9.2pf	Y		
		50pf	Z		

Jan-17	N	Jan-18	A
Feb-17	P	Feb-18	B
Mar-17	Q	Mar-18	C
Apr-17	R	Apr-18	D
May-17	S	May-18	E
Jun-17	T	Jun-18	F
Jul-17	U	Jul-18	G
Aug-17	V	Aug-18	H
Sep-17	W	Sep-18	J
Oct-17	X	Oct-18	K
Nov-17	Y	Nov-18	L
Dec-17	Z	Dec-18	M

备注：年份印字代码原则按奇偶年两年一个循环

HUILONG ELECTRONIC (JINHUA) CO.,LTD


H0-R-4-014



TYPE HL SEAM SEALED X'TAL

RELIABILITY SPECIFICATIONS






NO.	TEST ITEM	TEST METHODS
1	DROP TEST	Device are dropped from a height of 150 cm onto 2 mm thickness stainless plate executing 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	VIBRATION	Frequency range 10 ~ 2000 Hz Amplitude 1.5 mm Sweep Time 20 minute Test Time 2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature $245^{\circ}\text{C} \pm 5^{\circ}\text{C}$ Material H63A (Silver 2 ~ 3 %) Immersion depth 0.5 mm minimum Immersion time 3 ± 0.5 seconds Flux Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into $260 \pm 5^{\circ}\text{C}$ solder pot, above 180°C is 90 ~ 120 sec.
6	LOW TEMP. STORAGE	Leave at $-55^{\circ}\text{C} \pm 2^{\circ}\text{C}$ for 1000 ± 12 hours
7	HIGH TEMP. STORAGE	Leave at $125^{\circ}\text{C} \pm 2^{\circ}\text{C}$ for 1000 ± 12 hours
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle






TYPE HL SEAM SEALED X'TAL

DIMENSIONS




1	Quartz Blank
2	Electrode
3	Lid
4	Base
5	Conductive adhesive






TYPE HL SEAM SEALED X'TAL

SUGGESTED IR REFLOW PROFILE



Total Time : 200 Sec.Max
Solder melting point : 185°C

PACKING



1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.





HUILONG ELECTRONIC (JINHUA) CO.,LTD

H0-R-4-014



TYPE HL SEAM SEALED X'TAL

PACKING



HUILONG ELECTRONIC (JINHUA) CO.,LTD