



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer):

客戶料號 (Customer P/N):

興華鑫型號 (Supplier P/N):

HC3040-L100MM

產品名稱 (Description):

蜂鸣器 (Buzzer)

產品規格 (Specification):

30*6.0MM 4KHZ 无源压电式

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)		
	審核	檢查	制作
	唐国兴	唐玉来	吴银娟
	日期: 2022 年 04 月 19 日 版次: A		

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: www.jsxhxdz.com

深圳市兴华鑫电子科技有限公司

产品规格内容

Customer:			Part No:		
Product: Piezoelectric Buzzers			XHXDZ Part No: XHXDZ-3040 引线无源压电		
Technical Terms					
Resonant Frequency (KHZ)			4.0±0.5		
Rated Voltage (V _{P-P})			5.0		
Operating Voltage (V _{P-P})			1~30		
Max. Current Consumption at Rated Voltage (mA)			2.0		
Capacitance at 1000Hz (Pf)			32000±30%		
Min. Sound Output at 10cm at Rated Voltage (dB)			85		
Operating Temperature (°C)			-20~+60		
Storage Temperature (°C)			-30~+70		
Housing Material			ABS(Black)		
Environmental Protection Regulation			RoHS		
Buzzer			Soldering Parameter		
Soldering process			Temp.(°C)	Time(Sec.)	Times
Inclusive Lead		Reflow soldering	230±10	above 170°C time 40~70	2
		Wave soldering	245±5	3~6	1~2
		Manual soldering	330±10	1~2	1~2
Lead Free		Reflow soldering	245±15	above 180°C time 40~70	3
		Wave soldering	260±5	4~8	2~3
	★	Manual soldering	350±10	1~3	2~3

Remark: ★XHXDZ Instance Soldering Process

APPEARANCE DRAWING Tol : ± 0.5 Unit: mm

