



浙江汇隆晶片技术有限公司
Zhejiang Huilong Crystals Technology Co.,Ltd

SPECIFICATION FOR APPROVAL

CUSTOMER

NOMINAL FREQUENCY

25.000000 MHz

HOLDER TYPE

HC-49US

SPEC. NO. (P/N)

HA25000F012

CUSTOMER P/N

ISSUE DATE

Feb.24,2023

APPROVED	PREPARED	QA
彭达梅	金文波	訾红华
APPROVED BY CUSTOMER:		AVL Status
Please return one copy with approval to HLC		

浙江省金华市经济开发区工业园区秋涛北街399号

No.399 Qiutao North Str.,Industrial Area,Economic

Development Zone,Jinhua,Zhejiang,China

TEL: 0086-579-82273331

FAX: 0086-579-82273198

<http://www.cn-hlc.com>



RoHS Compliant (Pb- Free)



TYPE HA SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HA25000F012


Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	25.000000			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	CL	20			pF	
Frequency Tolerance	FT	± 20			ppm	at 25°C $\pm 3^\circ\text{C}$
Frequency Stability		± 30			ppm	with working temperature Reference to 25°C frequency
Working temperature range	TR	-40~85			°C	
Drive Level	DL	100			μW	
Series Resonant Resistance RR	CI/RR	40			Ω	Max.
Shunt Capacitance C0	C0	7			pF	Max.
Aging		± 5			ppm/yr.	
Storage temperature range		-40 ~ 125			°C	

Zhejiang Huilong Crystals Technology Co.,Ltd



TYPE HA SEAM SEALED X'TAL

MARKING



HLC: HLC Use Code x: CL Code

x: Date Code

CL	Code	CL	Code	CL	Code
0pf	0	7.5pf	H	11.2pf	a
6pf	1	11pf	I	11.4pf	b
8pf	2	8.5pf	J	13.5pf	d
10pf	3	7.1pf	K		
12pf	5	19pf	L		
15pf	6	12.5pf	M		
16pf	7	27pf	N		
18pf	8	7.3pf	O		
20pf	9	13pf	P		
22pf	A	11.5pf	Q		
25pf	B	7pf	R		
28pf	C	14pf	S		
30pf	D	23pf	T		
32pf	E	11.1pf	U		
9.5pf	F	33pf	V		
9pf	G	10.5pf	W		
		9.2pf	Y		
		50pf	Z		

Jan-23	N	Jan-24	A
Feb-23	P	Feb-24	B
Mar-23	Q	Mar-24	C
Apr-23	R	Apr-24	D
May-23	S	May-24	E
Jun-23	T	Jun-24	F
Jul-23	U	Jul-24	G
Aug-23	V	Aug-24	H
Sep-23	W	Sep-24	J
Oct-23	X	Oct-24	K
Nov-23	Y	Nov-24	L
Dec-23	Z	Dec-24	M

备注：年份印字代码原则按奇偶年两年一个循环

Zhejiang Huilong Crystals Technology Co.,Ltd




TYPE HA SEAM SEALED X'TAL

RELIABILITY SPECIFICATIONS

NO. TEST ITEM
H0-R-4-014


TEST METHODS

1	DROP TEST	Device are dropped from a height of 75 cm onto 3 mm thick wood to perform 3 times of random drops.	
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.	
3	VIBRATION	Frequency range	10 ~ 2000 Hz
		Amplitude	1.5 mm
		Sweep Time	20 minute
		Test Time	2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C	
		Temperature	245°C±5°C
		Material	H63A (Silver 2 ~ 3 %)
		Immersion depth	0.5 mm minimum
		Immersion time	3 ± 0.5 seconds
		Flux	Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into 260 ± 5°C solder pot, above 180°C is 90 ~ 120 sec.	
6	LOW TEMP. STORAGE	Leave at - 55 °C ± 2°C for 1000 ± 12 hours	
7	HIGH TEMP. STORAGE	Leave at 125 °C ± 2°C for 1000 ± 12 hours	
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle	




Zhejiang Huilong Crystals Technology Co.,Ltd

DIMENSIONS



Inner structure




Zhejiang Huilong Crystals Technology Co.,Ltd



TYPE HA SEAM SEALED X'TAL

SUGGESTED IR REFLOW PROFILE



Total Time: 200 Sec.Max

Solder melting point : 185°C


Zhejiang Huilong Crystals Technology Co.,Ltd



TYPE HA SEAM SEALED X'TAL

PACKING

DIMENSION: (mm) Packing Box



Packing quantity: 1000pcs per box and 10 000pcs per container .

Zhejiang Huilong Crystals Technology Co.,Ltd
