

# KBJ15005 thru KBJ1510

## 15.0 A Single-Phase Silicon Bridge Rectifier

Rectifier Reverse Voltage 50 to 1000V

### Features


- Ideal for printed circuit board mounting
- The plastic material used carries Underwriters Laboratory flammability recognition 94V-0
- Built-in printed circuit board stand-offs
- High case dielectric strength
- High temperature soldering guaranteed 260°C/5 seconds at 5 lbs (2.3kg) tension

### Mechanical Data

Case: Reliable low cost construction utilizing molded plastic technique

Terminals: Plated leads solderable per MIL-STD-202, Method 208

Mounting Position: Any



Dimensions in inches and (millimeters)

### Maximum Ratings & Thermal Characteristics

Rating at 25°C ambient temperature unless otherwise specified, Resistive or Inductive load, 60 Hz.  
For Capacitive load derate current by 20%.

| Parameter                                                                             | Symbol           | KBJ 15005    | KBJ 1501 | KBJ 1502 | KBJ 1504 | KBJ 1506 | KBJ 1508 | KBJ 1510 | unit               |
|---------------------------------------------------------------------------------------|------------------|--------------|----------|----------|----------|----------|----------|----------|--------------------|
| Maximum repetitive peak reverse voltage                                               | VRRM             | 50           | 100      | 200      | 400      | 600      | 800      | 1000     | V                  |
| Maximum RMS bridge input voltage                                                      | VRMS             | 35           | 70       | 140      | 280      | 420      | 560      | 700      | V                  |
| Maximum DC blocking voltage                                                           | VDC              | 50           | 100      | 200      | 400      | 600      | 800      | 1000     | V                  |
| Maximum average forward rectified output current at TC=100°C (with heatsink)          | IF(AV)           | 15.0         |          |          |          |          |          |          | A                  |
| Peak forward surge current single sine-wave superimposed on rated load (JEDEC Method) | IFSM             | 220          |          |          |          |          |          |          | A                  |
| Rating for fusing ( t<8.3ms)                                                          | I <sup>2</sup> t | 200          |          |          |          |          |          |          | A <sup>2</sup> sec |
| Operating junction and storage temperature range                                      | TJ, TSTG         | -55 to + 150 |          |          |          |          |          |          | °C                 |

### Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Resistive or Inductive load, 60Hz.  
For Capacitive load derate by 20 %.


| Parameter                                                                                 | Symbol | KBJ 15005 | KBJ 1501 | KBJ 1502 | KBJ 1504 | KBJ 1506 | KBJ 1508 | KBJ 1510 | Unit |
|-------------------------------------------------------------------------------------------|--------|-----------|----------|----------|----------|----------|----------|----------|------|
| Maximum instantaneous forward voltage drop per leg at 7.5A                                | VF     | 1.1       |          |          |          |          |          |          | V    |
| Maximum DC reverse current at rated TA =25°C<br>DC blocking voltage per element TA =125°C | IR     | 10<br>500 |          |          |          |          |          |          | μA   |

Notes: (1)Thermal resistance from Junction to Ambient on P.C.board mounting.


## Rating and Characteristic Curves ( $T_A = 25^\circ\text{C}$ Unless otherwise noted )

### KBJ15005 thru KBJ1510


**Fig. 1 Derating Curve for Output Rectified Current**




**Fig. 2 Maximum Non-repetitive Peak Forward Surge Current**



**Fig. 3 Typical Instantaneous Forward Characteristics**



**Fig. 4 Typical Reverse Characteristics**



**Fig. 5 Typical Junction Capacitance**

