



浙江汇隆晶片技术有限公司
Zhejiang Huilong Crystals Technology Co.,Ltd

SPECIFICATION FOR APPROVAL

CUSTOMER

NOMINAL FREQUENCY

8.000000 MHz

HOLDER TYPE

3225

SPEC. NO. (P/N)

HL08000057

CUSTOMER P/N

ISSUE DATE

Sep.27,2024

APPROVED	PREPARED	QA
		
APPROVED BY CUSTOMER:		AVL Status
Please return one copy with approval to HLC		

浙江省金华市经济开发区工业园区秋涛北街399号

No.399 Qiutao North Str.,Industrial Area,Economic

Development Zone,Jinhua,Zhejiang,China

TEL: 0086-579-82273331

FAX: 0086-579-82273198

<http://www.cn-hlc.com>



ISO9001
ISO14001



RoHS Compliant (Pb- Free)



TYPE HL SEAM SEALED X'TAL

ELECTRICAL SPECIFICATIONS

HLC Parts Number : HL08000057

Item	Symbol	Specifications				Notes
		Min	Type	Max	Units	
Nominal frequency	FO	8.000000			MHz	
Mode of Oscillation	OT	Fundamental				
Load Capacitance	CL	10			pF	
Frequency Tolerance	FT	± 10			ppm	at 25°C $\pm 3^\circ\text{C}$
Frequency Stability		± 80			ppm	with working temperature Reference to 25°C frequency
Working temperature range	TR	-40~125			°C	
Drive Level	DL	100			μW	
Series Resonant Resistance RR	CI/RR	180			Ω	Max.
Insulation Resistance	IR	>500			M Ω	
Shunt Capacitance C0	C0	7			pF	Max.
Aging		± 3			ppm/yr.	
Storage temperature range		-55 ~ 125			°C	

Zhejiang Huilong Crystals Technology Co.,Ltd



TYPE HL SEAM SEALED X'TAL

MARKING

HLC
* 8.03x

HLC: HLC Use Code x: CL Code x: Date Code

CL	Code	CL	Code	CL	Code
0pf	0	7.5pf	H	11.2pf	a
6pf	1	11pf	I	11.4pf	b
8pf	2	8.5pf	J	13.5pf	d
10pf	3	7.1pf	K	20.5pf	e
12pf	5	19pf	L	8.8pf	f
15pf	6	12.5pf	M	17pf	g
16pf	7	27pf	N	4.3pf	h
18pf	8	7.3pf	O	9.9pf	i
20pf	9	13pf	P	24pf	j
22pf	A	11.5pf	Q	9.4pf	m
25pf	B	7pf	R	8.2pf	n
28pf	C	14pf	S	6.8pf	q
30pf	D	23pf	T	90pf	r
32pf	E	11.1pf	U	5.6pf	t
9.5pf	F	33pf	V	5pf	u
9pf	G	10.5pf	W		
		9.2pf	Y		
		50pf	Z		


Jan-23	N	Jan-24	A
Feb-23	P	Feb-24	B
Mar-23	Q	Mar-24	C
Apr-23	R	Apr-24	D
May-23	S	May-24	E
Jun-23	T	Jun-24	F
Jul-23	U	Jul-24	G
Aug-23	V	Aug-24	H
Sep-23	W	Sep-24	J
Oct-23	X	Oct-24	K
Nov-23	Y	Nov-24	L
Dec-23	Z	Dec-24	M

备注：年份印字代码原则按奇偶年两年一个循环

Zhejiang Huilong Crystals Technology Co.,Ltd


RELIABILITY SPECIFICATIONS

NO.	TEST ITEM	TEST METHODS
1	DROP TEST	Device are dropped from a height of 150 cm onto 2 mm thickness stainless plate executing 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	VIBRATION	Frequency range Amplitude Sweep Time Test Time 10 ~ 2000 Hz 1.5 mm 20 minute 2 hours
4	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature Material Immersion depth Immersion time Flux 245°C±5°C H63A (Silver 2 ~ 3 %) 0.5 mm minimum 3 ± 0.5 seconds Rosin resin methyl alcohol solvent (1 : 4)
5	RESISTANCE TO SOLDERING HEAT	MIL - SLD -202, Method 210, Condition I or J 10 sec immersion into 260 ± 5°C solder pot, above 180°C is 90 ~ 120 sec.
6	LOW TEMP. STORAGE	Leave at - 40 °C ± 2°C for 16 hours
7	HIGH TEMP. STORAGE	Leave at 125 °C ± 3°C for 72 hours
8	THERMAL SHOCK	Total 100 cycles of the following temperature cycle




Zhejiang Huilong Crystals Technology Co.,Ltd

DIMENSIONS




Zhejiang Huilong Crystals Technology Co.,Ltd

SUGGESTED IR REFLOW PROFILE




Total Time: 200 Sec.Max
Solder melting point : 185°C

PACKING



	W	A ₀	B ₀	K ₀	E	F	P	P ₀	P ₂	D ₀	D ₁	T
3225	8.0±0.3	2.70±0.1	3.40±0.1	0.80±0.1	1.75±0.1	3.5±0.1	4.0±0.1	4.0±0.1	2.0±0.1	1.55±0.05	1.0±0.1	0.25±0.05




	A	W	T	N	C	D	E	G
3225	178±2.0	9.5±0.5	1.4±0.2	60.2±0.5	20.2±1.0	13.2±0.5	2.5±0.5	12±1.4

1. 230mm minimum leafer which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.

Zhejiang Huilong Crystals Technology Co.,Ltd

PACKING



Zhejiang Huilong Crystals Technology Co.,Ltd