

**POLYMER PTC
RESETTABLE FUSE**




电路保护元器件专业制造商
Part Number: TLC-TRM055

1. Physical Dimensions

Unit:mm

P/N	A	B	C	D	E	Lead
	Max.	Max.	TYP.	Nor.	Max.	Φ
TRM055	19.8	24.9	5.1	7.6	4.5	0.80



Logo
M 055 Holding Current
Max. Interrupt voltage
XX Lot No.

2. Electrical Characteristics


P/N	I _H	I _T	V _{max} OP V _{ac}	I _{max}	V _{max} Interrupt V _{rms}	T _{trip} (Max time to trip)		P _d typ	R _{min}	R _{max}	R1 _{max}
	(A)	(A)	(V)	(A)	(V)	Current(A)	time(S)	(W)	(Ω)	(Ω)	(Ω)
TRM055	0.55	1.25	240	7.0	265	2.75	26.0	3.4	0.45	0.84	1.45

- I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.
- I_T: Tripping Current minimum current at which the device will trip in 25°C still air.
- V_{max}: Maximum voltage device can withstand without damage at rated current.
- I_{max}: Maximum fault current device can withstand without damage at rated voltage.
- T_{trip}: Maximum time to trip(s) at assigned current.
- P_dtyp: Rated working power.
- R_{min}: Minimum resistance of device prior to trip at 25°C.
- R_{max}: Maximum resistance of device prior to trip at 25°C.
- R1_{max}: Maximum resistance of device is measured one hours post reflow at 25°C.

3. Thermal Derating (Maximum ambient operating temperature)

P/N	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
TRM055	0.87	0.76	0.65	0.55	0.44	0.39	0.33	0.28	0.21

4. Wave Soldering Parameters



5. Package Information

Packing quantity: 500pcs/bag
Tape and Reel Specifications:
Devices taped using EIA468-B/IEC286-2 standards.
Storage Condition: 0°C ~35°C, ≤70%RH, 2 Years

6. Agency Recognition: TUV



Caution: Operation beyond the rated voltage or current may result in rupture electrical arcing or flame. Specifications are subject to change without notice.

Web: www.tlcet.com.cn www.winvast.cn
TEL: 86-0769-3892 0554 FAX: 86-0769-8793 2077 E-mail: Tina@tlcet.com.cn
Address: No. 18, 5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710

Revision: D
Date: 2022-08-01

