





RoHS2.0+REACH



SECTION:A-A




A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NOTES:

SPECIFICATION:

1. CURRENT RATING: 5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES
9. DRAWINGS MARKED "*"FOR QIP DIMENSION.



6	接薄片	Ni Overall 50u"min (±4%)	SUS316L-1/2H T=0.12mm	1PCS
5	中夹片	SUS 301R-H Ni:50u" Min Matte Tin: 100u"Min 环保 盐雾24H	SUS301R-H T=0.15mm	1PCS
4	SHELL	Ni:50u"min (可焊膜) 环保 盐雾24H	SUS304 1/2H T=0.30mm	1PCS
3	CONTACT	Ni:50~80u"Tin100~180u" Au:1u"Min环保 盐雾24H ORANGE	C7025 T=0.15mm	1SET
2	CONTACT	Ni:50~80u"Tin100~180u" Au:1u"Min环保 盐雾24H ORANGE	C7025 T=0.15mm	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	LCP E130i 30%GF	1PCS
NO.	DESCRIPTION	FINISH/COLOR	MATERIAL	QTY

CHIN-BAN
Electronic Technology

DESCRIPTION: USB C TYPE 母座单排16Pin沉板0.8mm LCP蓝色

PART NO:	USBC1-AF-047
----------	--------------

REV: 1.0

OLD CODE:	
-----------	--

SIZE: A4

DRAWING NO:

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

$$.X:=\pm 0.30$$
$$.X^\circ := \pm 2^\circ$$
$$.XX := \pm 0.25$$
$$.XX^\circ := \pm 1^\circ$$
$$.XXX := \pm 0.15$$
$$.XXX^\circ := \pm 0.5^\circ$$

UNIT: MM

PROJECTION:

SCALE: 1:1

SHEET: 1 / 1

PART NO:	USBC1-AF-047
----------	--------------

REV: 1.0

OLD CODE:	
-----------	--

SIZE: A4

DRAWING NO: