







RoHS2.0+REACH



外壳DIP脚长度
(DIM:A=3.00)



SPECIFICATION
MATERIAL
See drawing
STANDARD DATA
Rating current:5A
ELECTRICAL
Insulator resistance:100Mohms Min.
Withstanding voltage:100VAC/minute
Contact resistance:40mohms Max
MECHANICAL
Mating force:5~20N Max.
Unmating force:6~20N Min.
Durability:10000 cycles Min.
DRAWINGS MARKED "⊗" FOR FAI DIMENSION.

NO. 序号	PARTS NAME 名称	QTY 用量	MATERIAL 材质	FINISH 处理
1	长端子	1SET	C7025 T=0.15MM	半金雾锡1U" Min
2	短端子	1SET		
3	长端子Molding	1PCS	LCP 黑色	BLACK
4	短端子Molding	1PCS		
5	BMI弹片	1PCS	SUS301 T=0.10MM	NI 50μ" Min
6	BMI弹片Molding	1PCS	LCP	BLACK
7	SHELL	1PCS	SUS304 T=0.20MM	NI 50μ" Min
8	卡勾	1PCS	SUS301 T=0.40MM	NI 50μ" Min SN 100u" min
1	长端子	1SET		
2	短端子	1SET	C7025 T=0.15MM	半金雾锡30U" Min

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXN1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXN2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:	GENERAL TOLERANCE
Frank	.X:=±0.30 .X':=±2° .XX:=±0.25 .XX':=±1° .XXX:=±0.15 .XXX':=±0.5°
CHECKED:	UNIT: MM PROJECTION:
yangjie	SCALE: 1:1
APPROVAL:	SHEET: 1/1

CHIN-BAN
Electronic Technology

DESCRIPTION: USB TYPE-C 24PIN公头SMT, CONN, LCP黑色	
PART NO: USBC1-AM-041	REV: 1.0
OLD CODE:	
DRAWING NO:	SIZE: A4