








RoHS2.0+REACH



NOTES:
SPECIFICATION:

1. CURRENT RATING: 5A MAX
2. Dielectric Withstanding Voltage: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

PIN	Signal Name	Description	PIN	Signal Name	Description
A1	GND	Ground return	B12	GND	Ground return
A2	SSTxp1	Positive half of first SuperSpeed TX differential pair	B11	SSRXp1	Positive half of first SuperSpeed RX differential pair
A3	SSTXn1	Negative half of first SuperSpeed TX differential pair	B10	SSRXn1	Negative half of first SuperSpeed RX differential pair
A4	Vms	Bus Power	B9	Vms	Bus Power
A5	CC1	Configuration Channel	B8	SBu2	Sideband Use (SBU)
A6	Dp1	Positive half of the USB 2.0 differential pair-Position 1	B7	Dn2	Negative half of the USB 2.0 differential pair-Position 2
A7	Dn1	Negative half of the USB 2.0 differential pair-Position 1	B6	Dp2	Positive half of the USB 2.0 differential pair-Position 2
A8	SBu1	Sideband Use (SBU)	B5	CC2	Configuraation Channel
A9	Vms	Bus Power	B4	Vms	Bus Power
A10	SSRXn2	Negative half of second SuperSpeed RX differential pair	B3	SSTXn2	Negative half of second SuperSpeed TX differential pair
A11	SSRXp2	Positive half of second SuperSpeed RX differential pair	B2	SSTXp2	Positive half of second SuperSpeed TX differential pair
A12	GND	Ground return	B1	GND	Ground return



6	接地片	SUS316L T=0.12mm	No Plated	1PCS
5	中央片	SUS301R-H T=0.15mm	No Plated	1PCS
4	SHELL	SUS304R-1/2H T=0.30mm	Ni 50u" Plated	1PCS
3	CONTACT	C18400 T=0.12mm	Au, Sn SEE TABLE Ni50u" Plated	1SET
2	CONTACT	C18400 T=0.12mm	Au, Sn SEE TABLE Ni50u" Plated	1SET
1	HOUSING	PA9T(GP2450NH) 原料	BLACK/BLUE	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

.X:=±0.30

.XX:=±0.25

.XXX:=±0.15

.X°:=±2°

.XX°:=±1°

.XXX°:=±0.5°

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: USB4 Gen3 USB TYPE C 24pin母座 错位双贴板上

PART NO: USBC1-AF-056

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4