

# DATA SHEET

**SUNGMUN CODE :** MSDR-16H1 (LG)

**DESCRIPTION :** ROTARY DIP SWITCH


## **SUNGMUN ELECTRONICS CO., LTD.**

Address 301-302, Bucheon Technopark 345, Seokcheon-ro, Ojeong-gu  
Bucheon-si, Gyeonggi-do, Korea  
TEL. +82-32-328-1941~4  
FAX +82-32-328-1945  
E-mail sungmun@sungmun.co.kr  
Website www.sungmun.com



| REV NO. | DATE | REVISION | DR | CH | APP |
|---------|------|----------|----|----|-----|
| △       |      |          |    |    |     |

SPECIFICATION

- Rating : 100mA, DC 42V (Switching)  
400mA, DC 42V (None-Switching)
- Contact Resistance : 80mΩ Max
- Insulation Resistance : 100MΩ Min
- Operating Force : Max 250gf·cm
- Life cycle : 25,000 steps
- Sealing : IP67 (Dust & Water proof)
- Packing : 65pcs Tube




ACTUATOR





| Real Coded |   |   |   |   |   |   |
|------------|---|---|---|---|---|---|
|            | C | 1 | 2 | 4 | 8 |   |
| 0          | ● |   |   |   |   | 0 |
| 1          | ● | ● |   |   |   | 1 |
| 2          | ● |   | ● |   |   | 2 |
| 3          | ● | ● | ● |   |   | 3 |
| 4          | ● |   |   | ● |   | 4 |
| 5          | ● | ● |   | ● |   | 5 |
| 6          | ● |   | ● | ● |   | 6 |
| 7          | ● | ● | ● |   |   | 7 |
| 8          | ● |   |   |   | ● | 8 |
| 9          | ● | ● |   |   | ● | 9 |
| 10         | ● |   | ● |   | ● | A |
| 11         | ● | ● | ● |   | ● | B |
| 12         | ● |   |   | ● | ● | C |
| 13         | ● | ● |   | ● | ● | D |
| 14         | ● |   | ● | ● | ● | E |
| 15         | ● | ● | ● | ● | ● | F |

16 Positions



P.C.B DIMENSION (Top View)



| Din ISO-2768-1m |       |      |      |        |         |
|-----------------|-------|------|------|--------|---------|
| Ranges          | 0.5~3 | 3~6  | 6~30 | 30~120 | 120~400 |
| Tolerance       | ±0.1  | ±0.1 | ±0.2 | ±0.3   | ±0.5    |

| DRAW/DESIGNED               | CHECKED    | APPROVED   |      | G.TOL | TITLE     | MINI ROTARY DIP SWITCH |      |
|-----------------------------|------------|------------|------|-------|-----------|------------------------|------|
| H.S LEE                     | K.N KIM    | W.J LEE    |      | --    |           |                        |      |
| 2024-03-06                  | 2024-03-06 | 2024-03-06 | UNIT | SCALE | MODEL NO. | MSDR-16H1(LG)          | REV. |
| SUNGMUN ELECTRONICS CO.,LTD |            |            |      | SIZE  | DRAW NO.  | MSDR-16H1(LG)-01       | 01   |
|                             |            |            |      | A4    |           |                        |      |

## 1. Style:

This specification describes "7.4X7.4 size of Mini Rotary Dip Switch" which is M series.

1.1 Operating / Storage Temperature Range : -60°C ~ +125°C

## 2. Rating:

2.1 None-Switching : 400 mA, DC 42V

2.2 Switching : 100 mA, DC 42V

3. Type of Actuation : Rotating

## 4. Electrical Characteristics

| ITEM | DESCRIPTION                     | TEST CONDITIONS                                                                                                                                                  | REQUIREMENTS                                                             |
|------|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| 4-1  | Visual Examination              | By visual examination check without any out pressure & testing.                                                                                                  | There shall be no defects that affect the serviceability of the product. |
| 4-2  | Contact Resistance              | ① To be measured between the two terminals associated with each switch pole.<br>② Measurements shall be made with a 1kHz shall current contact resistance meter. | 80mΩ max. (initial)                                                      |
| 4-3  | Insulation Resistance           | 250V DC                                                                                                                                                          | 100 MΩ min.                                                              |
| 4-4  | Dielectric withstanding Voltage | 250V AC(50Hz or 60Hz)shall be applied between all the adjacent terminal and between the terminal and the frame for 1 minute.                                     | There shall be no breakdown or flashover.                                |

## 5. Mechanical Characteristics

| ITEM | DESCRIPTION     | TEST CONDITIONS                                                                                                                                  | REQUIREMENTS                                                                           |
|------|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|
| 5-1  | Operation Force | Operating direction shall be clockwise or counter clockwise direction                                                                            | 250gf•cm max                                                                           |
| 5-2  | Operation Life  | Measurements shall be made following the test set forth below:<br>1)Rate of operation: 15~20 cycles/ minute<br>2)Step of operation: 25,000 steps | 1)As shown in item 4-3,4-4<br>2)Contact Resistance:<br>200mΩ max<br>3)Final-after test |


## 6. Environmental Characteristics

| ITEM | DESCRIPTION                 | TEST CONDITIONS                                                                                                                                                                                                                    | REQUIREMENTS                                                                                               |
|------|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|
| 6-1  | Resistance Low Temperature  | Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made:<br>1)Temperature: -60°C ±3°C<br>2)Time: 96 hours                               | 1)As shown in item 4-3, 4-4, 5-1<br>2)Contact Resistance:<br>200mΩ max                                     |
| 6-2  | Resistance High Temperature | Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made:<br>1)Temperature: 125°C ±2°C<br>2)Time: 96 hours                               | 1)As shown in item 4-3, 4-4, 5-1<br>2)Contact Resistance:<br>200mΩ max                                     |
| 6-3  | Resistance Humidity         | Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made:<br>1)Temperature: 40°C ±2°C<br>2)Relative humidity: 90~95%<br>3)Time: 96 hours | 1)As shown in item 4-4, 5-1<br>2)Contact Resistance:<br>200mΩ max<br>3)Insulation Resistance:<br>10 MΩ min |


## 7. This item is "RoHS" Compliant

8. Manual Soldering : Max 350°C, 3 sec.

9. Wave Soldering Conditions:



10. Reflow Soldering Conditions: (SMD type only)



## 10-1 Condition for Soldering

| Profile Feature                                                                                | Pb-Free Assembly                |
|------------------------------------------------------------------------------------------------|---------------------------------|
| Average Ramp-UP Rate(Ts max to TP)                                                             | 3°C/second max                  |
| Preheat<br>- Temperature Min(Ts min)<br>- Temperature Max(Ts max)<br>- Time (ts min to ts max) | 150°C<br>200°C<br>60-180seconds |
| Time maintained above:<br>- Temperature (TL)<br>- Time (tL)                                    | 217°C<br>60-150seconds          |
| Peak/Classification Temperature(TP)                                                            | 260°C +0°C/ -5°C                |
| Time within 5°C of actual Peak Temperature(TP)                                                 | Min 30 seconds                  |
| Ramp-Down Rate                                                                                 | 6°C/sec max                     |
| Time 25°C to Peak Temperature                                                                  | 8 minutes max                   |