



General Description


Glass passivated triacs in a plastic envelope, intended for use in applications requiring high bidirectional transient and blocking voltage capability and high thermal cycling performance.

Typical applications include motor control, industrial and domestic lighting , heating and static switching.

1. ANODE

2. ANODE


3. GATE



TO-252-2L

Package Marking and Ordering Information

Product ID	Pack	Packing Method	Qty(PCS)
BTB08-800	TO-252-2L	Tape and Reel	2500



Maximum Ratings (Ta=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Value	Unit
V_{DRM} / V_{RRM}	repetitive peak off-state voltage		800	V
$I_{T(RMS)}$	RMS on-state current		8	A
I_{TSM}	Non repetitive surge peak on-state current	$t = 20ms$ $T_j = 25^{\circ}C$	60	A
		$t = 16.7ms$ $T_j = 25^{\circ}C$	30	
$I^2 t$	$I^2 t$ for fusing	$t = 10 ms$	36	$A^2 s$
di/dt	Critical-rate of rise of commutation current I II III	$I_G = 2I_{GT}$ $t_r \leq 100ns$ $F = 120Hz$	50	A/us
I_{GM}	Peak Gate Current	$T_j = 125^{\circ}C$ $t_p = 20\mu s$	4	A
V_{GM}	Peak gate voltage	$T_j = 125^{\circ}C$	5	V
P_{GM}	Peak gate power	$T_j = 125^{\circ}C$	6	W
$P_{G(AV)}$	Average Gate Power Dissipation	$T_j = 125^{\circ}C$	0.5	W
T_j	Junction Temperature	-	-40 ~ 125	$^{\circ}C$
T_{stg}	Storage Temperature	-	-40 ~ 150	$^{\circ}C$




Electrical Characteristics (Ta=25°C unless otherwise specified)

Parameter		Symbol	Test conditions		Min	Typ	Max	Unit
Repetitive Peak Off-State Current Repetitive Peak Reverse Current		I _{DRM} , I _{RRM}	V _{DRM} =V _{RRM} T _J =25 °C				5	μA
			V _{DRM} =V _{RRM} T _J =125 °C				1	mA
Gate non-trigger voltage		V _{GD}	V _D = 1/2V _{DRM}		0.2			V
On-state voltage		V _{TM}	I _T = 6A, t _p =380us				1.65	V
Gate trigger current	I	I _{GT}	T ₂ (+), G(+)	V _D =12V R _L =100Ω			15	mA
	II		T ₂ (+), G(-)				20	
	III		T ₂ (-), G(-)		8		15	
	IV		T ₂ (-), G(+)				--	
Gate trigger voltage	I	V _{GT}	T ₂ (+), G(+)	V _D =12V R _L =100Ω		0.8	2	V
	II		T ₂ (+), G(-)			0.8	2	
	III		T ₂ (-), G(-)			0.8	2	
	IV		T ₂ (-), G(+)			--	--	
Holding current		I _H	V _D =12V , I _{GT} =100mA				30	mA
Critical-rate of rise of commutation voltage		dV/dt	V _{DM} =67%V _{DRM} Gate open T _J =125 °C				50	V/us
Rate of change of commutating voltage		(dI/dt) _c	V _{DM} =400V T _J =125 °C (dI/dt) _c =5.4A/ms Gate open				20	V/us
Turn-on time		t _{gt}	I _{TM} =16A , V _{DM} =V _{DRM(MAX)} I _G =0.1A, dI _G dt=5A uS				2	us



TO-252-2L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	0.483 TYP.		0.190 TYP.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 TYP.		0.114 TYP.	
L2	1.400	1.700	0.055	0.067
L3	1.600 TYP.		0.063 TYP.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 TYP.		0.211 TYP.	



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.