





RoHS2.0+REACH



SPECIFICATION

MATERIAL

See drawing

STANDARD DATA

Rating current:5A

ELECTRICAL

Insulator resistance:100Mohms Min.

Withstanding voltage:100VAC/minute

Contact resistance:40mohms Max


MECHANICAL

Mating force:5~20N

Unmating force:8~20N

Durability:10000 cycles

DRAWINGS MARKED "⊗" FOR FAI DIMENSION.



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCES:±0.05

ITEM	PARTS NAME	Q'TY	MATERIAL	FINISH/COLOR
1	SHELL	1	SUS316L	Ni Overall 50u"min
2	Insert molding CONTACT	2	LCP Ei310	Contact area:Gold 30u" Solder area:Matte tin 100~180u"BALCK
3	CONTACT	24	C7025 TM02	Contact area:Gold 30u" Solder area:Matte tin 100~180u"
4	Insert molding EMI spring	2	LCP Ei310	NO PLATED;BALCK
5	Emi spring	2	SUS301R-H	NO PLATED
6	LATCH	1	SUS301R-H	Underplating:Ni Overall 30~80u" Soldering area:Bright-Tin 100~180u"

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

.X:=±0.30

.X':=±2°

.XX:=±0.25

.XX':=±1°


.XXX:=±0.15

.XXX':=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1:1



SHEET: 1/1

CHIN-BAN
Electronic Technology

DESCRIPTION: USB C TYPE 24PIN 3.2PLUG(圆形拉伸) LCP黑色

PART NO: USBC1-AM-039

REV: 1.0

OLD CODE:

DRAWING NO:

SIZE: A4

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING