

Transient Voltage Suppressors (TVS) Data Sheet

Description

The SMAJ6.8CA is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events

Features

- For surface mounted applications in order to optimize board space
- Low leakage
- Glass passivated junction
- Low inductance
- Excellent clamping capability
- 400W peak pulse power capability at 10/1000μs waveform
- Fast response time
- Typical IR less than 5μA above 12.8V
- High Temperature soldering: 260°C /40 seconds at terminals
- Typical maximum temperature coefficient $\Delta V_{BR} = 0.1\% \times V_{BR}@25^{\circ}\text{C} \times \Delta T$
- Plastic package has Underwriters Laboratory Flammability 94V-0
- Matte tin lead-free Plated
- Halogen free and RoHS compliant
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC 61000-4-2 ESD 30KV(Air),30KV(contact)


Breakdown Voltage

5.8 V

Peak Pulse Power

400 W

DO-214AC(SMA)



Bi-directional



Uni-directional



Applications

TVS devices are ideal for the protection of I/O interfaces, VCC bus and other vulnerable circuits used in Telecom, Computer, Industrial and Consumer electronic applications

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	VALUE	SYMBOL
Peak Pulse Power Dissipation with a 10/1000μs waveform (Fig.1)(Note 1), (Note 2)	P_{PPM}	400	W
Peak Pulse Current with a 10/1000μs waveform.(Note1, Fig.3)	I_{PP}	See Next Table	A
Power Dissipation on Infinite Heat Sink at TL=75° C	$P_{M(AV)}$	1.0	W
Peak Forward Surge Current, 8.3ms Single Half Sine Wave (Note 3)	I_{FSM}	40	A
Maximum Instantaneous Forward Voltage at 25A for Unidirectional Only(Note 4)	V_F	3.5/5.0	V
Operating junction and Storage Temperature Range	T_J, T_{STG}	-55 to +150	°C
Typical thermal resistance junction to lead	$R_{\theta J-L}$	30	°C /W
Typical thermal resistance junction to ambient	$R_{\theta J-A}$	120	°C /W

Note :

(1) Non-repetitive current pulse, per Fig. 3 and derated above Ta = 25°C per Fig. 2.

(2) Mounted on 5.0mm x 5.0mm (0.03mm thick) Copper Pads to each terminal.


(3) 8.3ms single half sine-wave, or equivalent square wave, Duty cycle = 4 pulses per minutes maximum.

(4) $V_F < 3.5V$ for $V_{BR} < 200V$ and $V_F < 6.5V$ for $V_{BR} > 201V$.

SMAJ6.8CA

400W SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSORS







● Package Outline Dimensions (SMA/DO-214AC)

	Symbol	Dimensions			
		Millimeters		Inches	
		Min.	Max.	Min.	Max.
	A	1.25	1.65	0.049	0.065
	B	3.95	4.65	0.156	0.183
	C	2.35	2.85	0.093	0.112
	D	1.98	2.41	0.078	0.095
	E	0.76	1.52	0.030	0.060
	F	-	0.203	-	0.008
	G	4.70	5.30	0.185	0.209
	H	0.15	0.31	0.006	0.012
	M	2.26	-	0.089	-
	J	2.10	-	0.085	-
	K	-	2.74	-	0.107

● Electrical Characteristics (Ta=25°C Unless otherwise specified)

Part Number	Marking	Reverse Stand-Off Voltage	Breakdown Voltage V_{BR} (V) @ I_T		Test Current	Maximum Clamping Voltage@ I_{PP}	Peak Pulse Current	Reverse Leakage @ V_{RWM}
		V_{RWM} (V)	Min.	Max.	I_T (mA)	V_C (V)	I_{PP} (A)	I_R (μ A)
SMAJ6.8CA	6V8CA	5.8	6.46	7.14	10	10.5	38.10	1000

● Ratings And Characteristics Curves ($T_a=25^\circ\text{C}$ Unless otherwise specified)




SMAJ6.8CA

400W SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSORS

Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SMA	R2	0.07	5000	10000	80000	11"
SMA	R3	0.07	7500	15000	120000	13"

Soldering Parameters



Packaging (SMA/DO-214AC)

