


G108

▲ Show The Produced Unmber

▲ 可以生产的Pin数

▲ 60P	29.50	34.15
59P	29.00	33.65
58P	28.50	33.15
57P	28.00	32.65
56P	27.50	32.15
55P	27.00	31.65
▲ 54P	26.50	31.15
53P	26.00	30.65
52P	25.50	30.15
51P	25.00	29.65
▲ 50P	24.50	29.15
49P	24.00	28.65
48P	23.50	28.15
47P	23.00	27.65
46P	22.50	27.15
▲ 45P	22.00	26.65
44P	21.50	26.15
43P	21.00	25.65
42P	20.50	25.15
41P	20.00	24.65
▲ 40P	19.50	24.15
39P	19.00	23.65
38P	18.50	23.15
37P	18.00	22.65
▲ 36P	17.50	22.15
35P	17.00	21.65
34P	16.50	21.15
33P	16.00	20.65
32P	15.50	20.15
▲ 31P	15.00	19.65
30P	14.50	19.15
29P	14.00	18.65
28P	13.50	18.15
27P	13.00	17.65
26P	12.50	17.15
25P	12.00	16.65
▲ 24P	11.50	16.15
23P	11.00	15.65
▲ 22P	10.50	15.15
21P	10.00	14.65
▲ 20P	9.50	14.15
19P	9.00	13.65
18P	8.50	13.15
17P	8.00	12.65
▲ 16P	7.50	12.15
15P	7.00	11.65
14P	6.50	11.15
13P	6.00	10.65
12P	5.50	10.15
▲ 11P	5.00	9.65
10P	4.50	9.15
9P	4.00	8.65
8P	3.50	8.15
7P	3.00	7.65
▲ 6P	2.50	7.15
5P	2.00	6.65
4P	1.50	6.15
PIN	DIM=A	DIM=B



Note:

1. Material:

1.1 Housing: thermoplastic high temp.UL94V-0;
Color: natural.1.2 Latch: thermoplastic high temp.UL94V-0;
Color: black.

1.3 Terminal: copper alloy

1.4 Fitting Nail: copper alloy

2. Finsh:

2.1 Terminal:

Underplating: Au/matt Tin overall.

2.2 Fitting Nail:

Underplating: matt Tin overall.

PART NO. LEGEND:

F2DXXU-A1X1-E1R
R: REEL
E:H=2.0mmT:CONTACT:TIN PLATING
G:CONTACT:GOLD PLATING


1:PULL:LCP BLACK


A:HOUSING:LCP WHITE

U:SMT

XX:NO. OF POSITIONS

D:Easy-on Conn. RA SMT TYPE

剖面
B-B

G	E			DRAWING: Hu yatao	GENERAL TOLERANCE .X:=±0.15 .X*:=±5° .XX:=±0.10 .XX*:=±3° .XXX:=±0.05 .XXX*:=±1°			CHIN-BAN electronics (H.K) co., ltd		G					
	D														
	C			CHECKED: Tony	UNIT: MM	PROJECTION:		DESCRIPTION: 0.5mm PITCH FPC H2.0mm							
	B														
H	A			APPROVAL: yang jie	SCALE: 1/1		PART NO: F2DXXU-A1X1-E1R		REV: 1.0	H					
	NO.	DATE	DESCRIPTION	APPROVAL	SHEET: 1/1		DRAWING NO:		SIZE: A4						
		1		2		3		4		5		6		7	