







RECOMMENDED PCB LAYOUT



M/H	2.00	2.50	3.00	3.50	4.00
DIM E	1.95	2.40	2.90	3.40	3.90

SPECIFICATIONS:

- VOLTAGE/CURRENT RATING: 30V/AC, DC, 0.3A;
 - WITHSTANDING VOLTAGE: 100V AC/ONE MINUTE;
 - INSULATION RESISTANCE: 50M Ω MIN/100V DC.;
 - CONTACT RESISTANCE: 90m Ω MAX./1mA, 20mV AC, 1KHz;
 - DURABILITY: 30 CYCLES;
 - OPERATING TEMPERATURE RANGE: -40° C TO 125° C.
- MATERIAL:
- INSULATOR: LCP UL 94V-0 BLACK;
 - TERMINAL: PHOSPHOR BRONZE;
- PLATING:
- TERMINAL: CONTACT AREA: GOLD 0.05 μ m" MIN.
SMT LEAD: GOLD 0.025 μ m" MIN.
UNDERPLATING: NICKEL 1 μ m" MIN.

PIN NO.	DIM A	DIM B	DIM C	DIM D
10	4.60	1.60	3.55	1.00
12	5.00	2.00	3.95	1.00
20	6.60	3.60	5.55	1.00
24	7.40	4.40	6.35	1.20
30	8.60	5.60	7.55	1.50
34	9.40	6.40	8.35	1.50
40	10.60	7.60	9.55	3.20
50	12.60	9.60	11.55	3.20
60	14.60	11.60	13.55	3.20
70	16.60	13.60	15.55	3.20
80	18.60	15.60	17.55	3.20
90	20.60	17.60	19.55	3.20
100	22.60	19.60	21.55	3.20
120	26.60	23.60	25.55	3.20

6.0			
5.0			
4.0			
3.0			
2.0			
1.0			
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:
Frank
CHECKED:
yangjie
APPROVAL:

GENERAL TOLERANCE


.X:= $\pm$ 0.30 .X*:= $\pm$ 2°
.XX:= $\pm$ 0.20 .XX*:= $\pm$ 1°
.XXX:= $\pm$ 0.10 .XXX*:= $\pm$ 0.5°

UNIT: MM

PROJECTION:

SCALE: 1/1

SHEET: 1/1



CHIN-BAN
Electronic Technology

DESCRIPTION: BTB SOCKET P0.40

PART NO:

OLD CODE:

DRAWING NO: GY836S*** (M/H)

REV: 1.0

SIZE: A4