




MTA 156

TE Internal #: 3-641522-3
3 Position, Plug, Connector Assembly, Insulation Displacement (IDC), Wire-to-Wire, Tin (Sn), UL 94V-2, 3.96 mm [.156 in] Centerline, 1 Row, MTA 156

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Plug**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

Features

Product Type Features

Compatible With Discrete Wire Type	Solid, Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1
Number of Power Positions	3
Number of Signal Positions	0

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features



Primary Product Color	Orange
Cable Exit Angle	90°

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	50 µm[1.27 µin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
Wire Contact Termination Area Plating Thickness	2.03 µm[80 µin]
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A
Contact Type	Pin
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Strain Relief	With
Panel Mount Feature	Without
Contact Retention Type Within Housing	Locking Lance
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Wire & Cable IDC Installation Type	Feed Through
Centerline (Pitch)	3.96 mm [.156 in]
Housing Material	Nylon

Dimensions

Compatible Insulation Diameter Range	2.41 mm [.095 in]
--------------------------------------	-------------------



Connector Height	12.37 mm
Connector Length	15.85 mm
Wire Size	.8 – .9 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	2000
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 3-640600-3 03P MTA156 CONN ASSY 20AWG LF	 TE Part # 3-640599-3 03P MTA156 CONN ASSY 18AWG ORA	 TE Part # CAT-103156-WBHSM Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156	 TE Part # 3-640429-3 03P MTA156 CONN ASSY 24AWG WHT
 TE Part # 3-644860-3 03P MTA156 CONN ASSY 18AWG LF	 TE Part # 3-640602-3 03P MTA156 CONN ASSY 24AWG LF	 TE Part # 3-640426-3 03P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-640427-3 03P MTA156 CONN ASSY 20AWG YEL ORA
 TE Part # 3-640428-3 03P MTA156 CONN ASSY 22AWG RED	 TE Part # 3-640472-3 03P MTA156 ASSY ON TAPE LF	 TE Part # 640643-3 03P MTA156 COVER F/T	 TE Part # 640551-3 03P MTA156 COVER
 TE Part # 643067-3 03P MTA156 MOLDED COVER	 TE Part # 3-640430-3 03P MTA156 CONN ASSY 26AWG BLU	 TE Part # 643071-3 03P MTA156 FD-THRU COVER	 TE Part # 3-640601-3 03P MTA156 CONN ASSY 22AWG LF

Also in the Series | MTA 156



Connector Caps & Covers(89)

Connector Contacts(4)

Connector Hardware(2)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(677)

Power Contacts(3)

Rectangular Power Connectors(1178)

Wire-to-Board Headers & Receptacles (677)

Customers Also Bought

TE Part #35115
SPLICE,N CE 22-14

TE Part #59804-1
MAINTENANCE TOOL

TE Part #87309-9
MOD V RECP PLTD 30 AU

TE Part #284049-2
TERMI-BLOK VERTICAL PLUG STACK

TE Part #641321-2
RECEPT PIDG FASTON 26-24 187

TE Part #643067-3
03P MTA156 MOLDED COVER

TE Part #3-643817-3
03P MTA156 CONN ASSY 18AWG ORA

TE Part #3-644042-4
04P MTA100 CONN ASSY LF

TE Part #1-770903-0
MINI UMNL PIN 22-18 AWG AU

TE Part #5-103951-3
5X4 MTE PIN SR RIBBED .100CL

Documents



Product Drawings

03P MTA156 PSTD CONN ASSY ORNG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-641522-3_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-641522-3_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-641522-3_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English