

Electrical Characteristics($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	30	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=30A$	---	1.4	1.7	mΩ
		$V_{GS}=4.5V$, $I_D=30A$	---	1.9	2.6	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1.0	---	2.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=30V$, $V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	36	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2.5	---	Ω
Q_g	Total Gate Charge	$I_D=10A$	---	36.2	---	nC
Q_{gs}	Gate-Source Charge	$V_{DS}=12V$	---	11.6	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=4.5V$	---	8.7	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DS}=12V$ $V_{GS}=4.5V$, $R_L=0.5\Omega$ $R_{G(ext)}=4.7\Omega$	---	46	---	ns
T_r	Rise Time		---	72	---	
$T_{d(off)}$	Turn-Off Delay Time		---	76	---	
T_f	Fall Time		---	34	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	5300	---	pF
C_{oss}	Output Capacitance		---	580	---	
C_{rss}	Reverse Transfer Capacitance		---	590	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	180	A
I_{SM}	Pulsed Source Current		---	---	720	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=30A$, $T_J=25^{\circ}\text{C}$	---	0.80	1.2	V

Note :







1.The EAS data shows Max. rating . The test condition is $V_{DD}=30V$, $V_{GS}=10V$, $L=1\text{mH}$, $I_{AS}=40A$.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.


Cmos reserves the right to improve product design, functions and reliability without notice. Please refer to the latest version of specification.

Typical Characteristics



Package Dimension

TOLL-8 Unit :mm



SYMBOL		A	b	b1	b2	b3	b4	b5	b6	c	D	D1	D2	D3	D4	D5	e	E	E1
MILLIMETER	MIN.	2.2	0.7	9.7	0.36	0.05	0.3	1.1	3	0.4	10.28	10.98	3.2	7.15	3.59	3.26	1.1	9.8	7.4
	TYP.	2.3	0.8	9.8	0.45	0.1	0.4	1.2	3.1	0.5	10.38	11.08	3.3				1.2	9.9	7.5
	MAX.	2.4	0.9	9.9	0.55	/	0.5	1.3	3.2	0.6	10.55	11.18	3.4				1.3	10	7.6
SYMBOL		E2	E3	E4	H	H1	K	L	L1	L2	L3	L4	P	θ	aaa	ccc	ddd	eee	
MILLIMETER	MIN.	0.3	8.5	9.46	11.5	6.55	4.08	1.6	0.5	0.5	1	0.13	2.85	10° REF	0.2	0.2	0.25	0.2	
	TYP.	0.4			11.68	6.65	4.18	1.9	0.7	0.6	1.2	0.23	3						
	MAX.	0.5			11.85	6.75	4.28	2.1	0.9	0.7	1.3	0.33	3.15						