




2P

3P



4P~30P



P.C.B. LAYOUT
TOLERANCE:±0.05

Ordering Information:

A1255WR-S-XP - LCP - ***
1 2 3

1.Part NO.

2.Material:

(Blank): Nylon 9T,UL94V-0(Beige)

LCP: LCP,UL94V-0(Beige)

6T: Nylon 6T,UL94V-0(Beige)

3.Finish:

(Blank): Tin over Nickel

G: Gold over Nickel

SPECIFICATIONS:

Current Rating: 1A AC,DC

Voltage Rating: 150V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 30mΩ Max.

Insulation Resistance: 500MΩ Min.

Withstanding Voltage: 500V AC/minute

Pin Material: Brass

Solder Tabs: Brass

Ordering Information & Dimensions

Part NO.	Dimensions(mm)	
	A	B
A1255WR-S-2P	1.25	7.45
A1255WR-S-3P	2.50	8.70
A1255WR-S-4P	3.75	9.95
A1255WR-S-5P	5.00	11.20
A1255WR-S-6P	6.25	12.45
A1255WR-S-7P	7.50	13.70
A1255WR-S-8P	8.75	14.95
A1255WR-S-9P	10.00	16.20
A1255WR-S-10P	11.25	17.45
A1255WR-S-11P	12.50	18.70
A1255WR-S-12P	13.75	19.95
A1255WR-S-13P	15.00	21.20
A1255WR-S-14P	16.25	22.45
A1255WR-S-15P	17.50	23.70
A1255WR-S-20P	23.75	29.95
A1255WR-S-21P	25.00	31.20
A1255WR-S-25P	30.00	36.20
A1255WR-S-30P	36.25	42.45



CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE	
mm	1:1	1 of 1	1.25mm PITCH	
DRWN	CHK'D	APPR	RIGHT-ANGLE WAFER - SMD TYPE	
Chengbiao Ye	Diankui Wan	Jack Yin	ULTRA LOW PROF ILE	
General Tolerances			DRAWING NO.	REV
x,xx±0.25 x,xxx±0.20 x,xxxx±0.15 ANGLES ±1°			A1255WR-S-XP-LCP	A0
THIRD ANGLE PROJECTION				

REV	DESCRIPTION	DATE
A0	NEW RELEASE	2005.05.10