


SMD LVPECL Crystals

STARWAVE

Oscillators-Differential Output 3.2x2.5x0.95mm EC Series



Features


- > 3rd overtone solution.
- > 3.3V and 2.5V operation available.
- > LVPECL output , output frequencies 50MHz to 200MHz.
- > Excellent low phase noise and jitter.
- > Tri-State function available.
- > Applications; Fibre Channel , Gigabit Ethernet , Serial ATA , Serial Attached SCSI , PCI-Express,SDH / SONET.
- > RoHS Compliant / Pb Free.

Quartz
Oscillators

Electrical Specifications

Item / Type	EC
Output Type	LVPECL
Output Load	50Ω to VDD - 2V
Oscillation Mode	3rd Overtone
Supply Voltage	2.5V , 3.3V
Frequency Range	50 ~ 200 MHz
Overall Frequency Stability	± 30 ppm, ± 50 ppm or specify
Operating Temperature Range	- 40 ~ + 85 °C,- 40 ~ + 105 or specify
Storage Temperature Range	- 55 ~ + 125 °C
Voltage Vol(Min.) / Voh(Max.)	VDD - 1.62V / VDD - 1.025 V
Rise (Tr) / Fall (Tf) Time (20%~80%)	1nS Max
Supply Current	80 mA Max.
Symmetry	45 ~ 55%
Start-up Time	10 mS Max.
Phase Jitter (12 KHz ~ 20 MHz)	0.2pS Max.

Dimensions




※ Pad dimension tolerance ±0.2 mm

Pin Function:

1. OE
2. NC
3. GND
4. OUT
5. $\overline{\text{OUT}}$
6. VDD

Land Pattern:



※ Power Supply Decoupling Capacitor is Required.

Units:mm

Remark : Specification subject to change without prior notice. Please confirm with our sales.[www. starwavecorp.com](http://www.starwavecorp.com)