





NOTES:

MATERIAL:

1. HOUSING MATERIAL
 2. CONTACT MATERIAL
 3. PLATING
- GLASS FILLED POLYESTER UL94V-0.
PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
GOLD PLATING OVER NICKEL.

ELECTRICAL:



1. VOLTAGE RATING
 2. CURRENT RATING
 3. CONTACT RESISTANCE
 4. INSULATION RESISTANCE
 5. DIELECTRIC WITHSTANDING RESISTANCE
- :125 VAC RMS.
:15 AMP.
:30 MILLIOHMS MAX.
:500 MEGOHMS MIN @ 500V DC.
:1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. DURABILITY
 2. PCB RETENTION PRE-SOLDER
- :750 CYCLES MIN.
:1 LB MIN.

ENVIRONMENTAL:

1. STORAGE
 2. OPERATION
- : -40°C~+85°C
: -25°C~+85°C



PC Board Layout

Component Side Shown

APPROVED:	DATE:	TITLE: C 深圳市灿科盟实业有限公司 km tw CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	CLIENT P/N	R-RJ45R08P-A201	UNIT	mm
SXA	2019-06-21	SCALE	free	REV.	A
TOLERANCE TABLE		FILE NO.	Ckmtw-RJ45-0197	HY04	
.0	±0.30				
.00	±0.20				
.000	±0.05				