


1. Features

- Advanced Trench technology
- $R_{DS(ON)}=2.4m\Omega$ (typ.) @ $V_{GS}=10V$
- Super Low Gate Charge
- Green Device Available
- Excellent CdV/dt effect decline
- 100% ΔV_{ds} TESTED
- 100% UIS TESTED

2. Pin configuration



TO-263



Pin	Function
1	Gate
2	Drain
3	Source

3. Ordering Information

Part Number	Package	Brand
KNB2803T	TO-263	KIA

4. Absolute maximum ratings

T _A =25°C unless otherwise specified				
Parameter	Symbol	Ratings	Unit	
Drain-to-Source Voltage (V _{GS} =0V)	V _{DS}	30	V	
Gate-to-Source Voltage (V _{DS} =0V)	V _{GS}	±20	V	
Continuous Drain Current ¹⁾	T _C =25°C	I _D	150	A
	T _C =100°C	I _D	95	A
Pulsed Drain Current @ Current-Pulsed ²⁾	I _{DM}	640	A	
Total Power Dissipation (T _C =25°C) ⁴⁾	P _D	150	W	
Avalanche Energy ³⁾	EAS	381	mJ	
Operation Junction and Storage Temperature Range	T _J , T _{STG}	-55 to 150	°C	

5. Thermal characteristics

Parameter	Symbol	Max.	Unit
Thermal Resistance, Junction-to-Case ¹⁾	R _{θJC}	1.0	°C/W

6. Electrical characteristics

(T_A=25°C, unless otherwise notes)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =250uA	30	-	-	V
Drain-Source Leakage Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V, T _C =25°C	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{GS} =V _{DS} , I _D =250uA	1.0	1.5	2.5	V
Static Drain-Source On-Resistance ²⁾	R _{DS(ON)}	V _{GS} =10V, I _D =30A	-	2.4	3.0	mΩ
		V _{GS} =4.5V, I _D =15A	-	3.2	4.0	mΩ
Gate Resistance	R _g	V _{DS} =0V, V _{GS} =0V, f=1.0MHz	-	1.8	-	Ω
Input Capacitance	C _{iss}	V _{DS} =15V, V _{GS} =0V, f=1.0MHz	-	3510	-	pF
Output Capacitance	C _{oss}		-	445	-	pF
Reverse Transfer Capacitance	C _{rss}		-	375	-	pF
Turn-On Delay Time	t _{d(on)}	V _{DS} =15V, V _{GS} =10V, R _G =2.0Ω, I _D =20A	-	9.5	-	ns
Rise Time	t _r		-	18.5	-	ns
Turn-Off Delay Time	t _{d(off)}		-	50	-	ns
Fall Time	t _f		-	18	-	ns
Total Gate Charge	Q _g	V _{DS} =15V, V _{GS} =10V, I _D =30A	-	80	-	nC
Gate-Source Charge	Q _{gs}		-	4.5	-	nC
Gate-Drain Charge	Q _{gd}		-	30	-	nC
Source-Drain Current (Body Diode) ^{1),5)}	I _{SD}	—	-	-	150	A
Diode Forward Voltage ²⁾	V _{SD}	V _{GS} =0V, I _{SD} =30A, T _J =25°C	-	-	1.2	V
Reverse Recovery Time	t _{rr}	T _J =25°C, I _F =30A, di/dt=100A/μs	-	18	-	nS
Reverse Recovery Charge	Q _{rr}		-	6.8	-	nC
Forward Turn-on Time	t _{on}	Intrinsic turn-on time is negligible (turn-on is dominated by LS +LD)				

Notes:

- 1) The data tested by surface mounted on a 1 inch² FR-4 board with 20Z copper.
- 2) The data tested by pulsed, pulse width≤300us, duty cycle≤2%.
- 3) The test condition is V_{DD}=20V, V_{GS}=10V, L=0.5mH, I_{AS}=38A.
- 4) The power dissipation is limited by 175°C junction temperature.
- 5) The data is theoretically the same as I_D and I_{DM}, in real applications, should be limited by total power dissipation.

7. Typical Characteristics




Fig1: Typical Output Characteristics




Fig 2: Typical Transfer Characteristics




Fig 3: On-Resistance VS. Drain Current




Fig 4: Maximum Continuous Drain Current VS. Case Temperature




Fig 5: Gate Charge Characteristics




Fig 6: Capacitance Characteristics




Fig 7: Normalized Breakdown Voltage VS. Junction Temperature




Fig 8: Normalized on Resistance VS. Junction Temperature




Fig 9: Maximum Safe Operating Area




Fig 10: Body Diode Forward Characteristics




Fig.11: Maximum Effective Transient Thermal Impedance, Junction-to-Case

8. Test Circuit & Waveform




Fig 12: Gate Charge Test Circuit and Waveforms




Fig 13: Resistive Switching Test Circuit and Waveforms




Fig 14: Unclamped Inductive Switching Test Circuit and Waveforms