


Description

XCH Semiconductor(XCH)has series Multi-EPI Super-Junction power MOSFET platforms for voltage up 500V to 1000 volts, bothwith design service and manufacturing capability, including cell,termination design and simulation.

The GSx25N65EF is a Low voltage N channel Multi-EPI Super-Junction power MOSFET sample with advanced technology to have better characteristics, such as fast switchingtime. low Ciss and Crss. low on resistance and excell entavalanche characteristics.



TO-247

TO-220F

Features


$R_{DS(ON)}=0.14\Omega$ @ $V_{GS} = 10V$

$V_{DS} = 650V$

Intrinsc fast-recovery body diode.

PKG

GS25N65EF	GSW25N65EF
TO-220F	TO-247



Absolute Maximum Ratings (TC = 25°C, unless otherwise specified)

Symbol	Parameter	GSW25N65EF	GSA25N65EF	Unit
V_{DS}	Drain-Source Voltage	650		V
I_D	Drain Current -Continuous (TC = 25°C) -Continuous (TC = 100°C)	25* 15*		A
I_{DM}	Drain Current - Pulsed	53		A
V_{GS}	Gate-Source voltage	± 30		V
E_{AS}	Single Pulsed Avalanche Energy	500		mJ
I_{AR}	Avalanche Current	4		A
E_{AR}	Repetitive Avalanche Energy	1.2		mJ
dv/dt	Peak Diode Recovery dv/dt	15		V/ns
dV_{DS}/dt	Drain Source voltage slope ($V_{DS}=480V$)	50		V/ns
P_D	Power Dissipation (TC = 25°C)	210	35	W
T_J, T_{STG}	Operating and Storage Temperature Range	-55 to +150		°C
T_L	Max. Lead Temperature for Soldering Purpose, 1/8" from Case for 5 Seconds	300		°C

Thermal Characteristics


Symbol	Parameter	GSW25N65EF	GSA25N65EF	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	0.58	3.7	°C/W
$R_{\theta CS}$	Thermal Resistance, Case-to-Sink Typ.	0.5	---	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	62	62	°C/W

■ Electrical Characteristics (T_J=25°C unless otherwise specified)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250μA, T _J = 25°C	650	--	--	V
		V _{GS} = 0V, I _D = 250μA, T _J = 150°C	--	700	--	V
ΔBV _{DSS} /ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250μA, Referenced to 25°C	--	0.6	--	V/°C
I _{BSS}	Zero Gate Voltage Drain Current	V _{bs} = 650V, V _{GS} = 0V -T _J =25 °C -T _J = 150°C	--	-- 10	1 -	μA μA
I _{GSSF}	Gate-Body Leakage Current, Forward	V _{GS} = 30V, V _{DS} = 0V	--	--	100	nA
I _{GSSR}	Gate-Body Leakage Current, Reverse	V _{GS} = -30V, V _{DS} = 0V	--	--	-100	nA
On Characteristics						
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	2	--	4	V
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} = 10V, I _D = 12A	--	0.12	0.14	Ω
g _{FS}	Forward Transconductance	V _{bs} = 40V, I _D = 12A	--	16	--	S
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} = 25V, V _{GS} = 0V, f = 1.0MHz	--	1650	-	pF
C _{oss}	Output Capacitance		--	90	-	pF
C _{rss}	Reverse Transfer Capacitance		--	9	--	pF
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} = 520V (Note 4)	--	28	--	ns
t _r	Turn-On Rise Time		--	19	--	ns
t _{d(off)}	Turn-Off Delay Time		--	140	--	ns
t _f	Turn-Off Fall Time		--	12	--	ns
Q _g	Total Gate Charge	V _{bs} = 520V, I _D = 12A	--	110	140	nC
Q _{gs}	Gate-Source Charge	V _{GS} = 10V (Note 4)	--	9	--	nC
Q _{gd}	Gate-Drain Charge		--	15	--	nC
Drain-Source Diode Characteristics and Maximum Ratings						
I _S	Maximum Continuous Drain-Source Diode Forward Current		--	--	25	A
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current		--	--	75	A
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0V, I _S = 12A	--	0.9	1.5	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0V, I _S = 12A dI _F /dt =100A/μs	--	190	--	ns
Q _{rr}	Reverse Recovery Charge		--	6	--	μC


Typical Performance Characteristics

Diagram 1: Power dissipation




$$P_{tot} = f(T_c)$$

Diagram 2: Safe operating area




$$I_D = f(V_{DS}); T_c = 25^\circ\text{C}; D = 0; \text{parameter: } t_p$$

Diagram 3: Safe operating area



$$I_D = f(V_{DS}); T_c = 80^\circ\text{C}; D = 0; \text{parameter: } t_p$$


Diagram 4: Max. transient thermal impedance



$$Z_{thJC} = f(t_p); \text{parameter: } D = t_p / T$$


Typical Performance Characteristics

Diagram 5: Typ. output characteristics




$I_D = f(V_{DS}); T_J = 25\text{ }^{\circ}\text{C}; \text{parameter: } V_{GS}$

Diagram 6: Typ. output characteristics




$I_D = f(V_{DS}); T_J = 125\text{ }^{\circ}\text{C}; \text{parameter: } V_{GS}$

Diagram 7: Typ. drain-source on-state resistance



$R_{DS(on)} = f(I_D); T_J = 125\text{ }^{\circ}\text{C}; \text{parameter: } V_{GS}$


Diagram 8: Drain-source on-state resistance



$R_{DS(on)} = f(T_J); I_D = 8.9\text{ A}; V_{GS} = 10\text{ V}$


Typical Performance Characteristics

Diagram 9: Typ. transfer characteristics




$I_D = f(V_{GS})$; $V_{DS} = 20V$; parameter: T_j

Diagram 10: Typ. gate charge




$V_{GS} = f(Q_{gate})$; $I_D = 8.9A$ pulsed; parameter: V_{DD}

Diagram 11: Forward characteristics of reverse diode



$I_F = f(V_{SD})$; parameter: T_j


Diagram 12: Avalanche energy



$E_{AS} = f(T_j)$; $I_D = 7.1 A$; $V_{DD} = 50 V$


Typical Performance Characteristics

Diagram 13: Drain-source breakdown voltage




$$V_{BR(DSS)} = f(T_j); I_D = 1 \text{ mA}$$

Diagram 14: Typ. capacitances



$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 250 \text{ kHz}$$

Diagram 15: Typ. Coss stored energy



$$E_{Coss} = f(V_{DS})$$