


SPECIFICATION FOR APPROVAL

CUSTOMER		CUST P/N.	
ITEM	Data Line Filter	Description	BCB0308WN-500
PART NO.	302-36502	DATE	2023.11.28
(1) DIMENSION(UNIT:mm) 		A	10.0±0.5 mm
		B	7.0±0.5 mm
		C	7.0 ±0.5 mm
		D	3.0±0.5 mm
		E	7.5 ± 0.5 mm
		F	5.0 ± 0.5 mm
		G	Ø0.6(REF) mm
		H	mm
(2)ELECTRICAL REQUIREMENTS			
TEST CONDITION		FREQUENCY	(3) TEST INSTRUMENTS
		VOLTAGE	LCR-METER:
L	50.0uH(REF)	100KHz 0.1V	WK3260B V HP4291A
Z	800Ω (Min)	100MHz 50mV	LCR-METER: V HP4291A
DCR	110.0mΩ (Max)	KHz V	LCR-METER: V HP4291A
IDC	1A(Max)	100KHz 0.1V	CURRENT SOURCE: WK3260B
		MHz V	GW PUNCTURE INSULATION TESTER HP4291A
(4)TURNS: 18Ts(REF)			
(5)MATERIAL LIST			
ITEM	MATERIAL	DESCRIPTION	UL NO.
1	CORE	P16材 T7×5×3-C	
2	WIRE	Ø0.22mm×2(2UEW+NY)	E197768
3	BASE	BD-025	E59481
4			
REMARK:		APPROVED	CHECKED DRAWN BY
		姜杰文	姜法宝 王艳

MINGSTAR ELECTRONIC CORP.