



1



2

3

4




□12.3麦拉





Technical requirements:

- 1、Unit: mm
- 2、Wire diameter: 0.
- 3、Material: Nickel-plated carbon steel(RoHS compliant)
- 4、Type: XMWDZ SMT clip spring
- 5、Processing: Heat-treated at 180° C
- 6、Size tolerance: ± 0.25 for unmarked dimensions
- 7、Quality: Free from surface contaminants ,
No base material defects
- 8、Contact number: 13459252012、0592-5216722
- 9、MLF12-14.5-0.5NN
- 10、Salt spray test: passes 24 Hours test (5% NaCl Solution)
- 11、Package: Bag-packed, MPQ:200PCS/bag



载带卷料方向



Note: ± 0.25 mm for unmarked dimensions;

The F value is centered on B0; The P2 value is centered on A0

- 1: 10 sprocket hole pitch cumulative tolerance ± 0.20 mm.
- 2: Carrier camber not to exceed 1mm in 250mm.
- 3: A0 and B0 measured on a plane 0.3mm above the bottom of the pocket.
- 4: K0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
- 5: All dimensions meet EIA-481-D requirements.
- 6: Material:Black polystyrene.
- 7: Thickness: 0.5 ± 0.05 mm.
- 8: Packing length per 13'' reel 4.4 Meters.
- 9: Component loader per 13'' reel:200pcs. Leave 10pcs empty at both ends.