

REV	CONTENT	CHK	DATE
V0.0	CONTENT	CXL	20.05.11

Electrical :


- | | | |
|--|----------------|------------------------|
| | UL | IEC |
| 1.Rated Voltage : | 300V | 450V |
| 2.Rated Current : | 30A | 24A |
| 3.Torque Value : | M3 , 4.43Lb.in | M3 , 0.5N.m |
| 4.Wire Range: | 26-10AWG | 1.5-4.0mm ² |
| 5.Stripping Length : | 7-8mm | |
| 6.Withstanding Voltage : | AC2500V/1Min. | |
| 7.Operating Temperature : | -40°C~+105°C | |
| 8.RoHS Compliance | | |
| 9.Safty Approval : | CE | |
| 10."★" is the key quality control point. | | |

TY636 - 7.62 - XXP - X X - 00

① ② ③ ④ ⑤ ⑥

- ① Sereies No. ④ 1 Single Pitch
2 Double Pitch
- ② Pitch ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White
- ③ Poles
02 02Contacts
03 03Contacts
... 24 24Contacts
- ⑥ Customer Request : 00--Standard

SECTION A-A



A	Total Pitch Tolerances in mm									Nominal dimension range in mm									$\perp$	$\equiv$	$-$	$//$		
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 0	over		over 0	over 100	over
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10	10	all	to 100	to 150	150
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3		0.3	0.2	0.3
6									5												6			

4	SCREW		XX		P	STEEL		Zn Plated	
3	BLOCK		XX		P	BRASS		Ni Plated	
2	PIN		XX		P	BRASS		Tin Plated	
1	HOUSING		XX		1	PA66 UL94V-0		SEE NOTE	
ITEM	NAME OF PART		NO. OF PART		Q'TY	MATERIAL		NOTE	
DWG.	CXL	DATE	20.05.11		SIZE	A4	UNITS	mm	SHEET/OF 1 / 1
CHK.		DATE			SCALE	1:1			
APP.		DATE			NAME	TY636-7.62-XXP-XX-00			
 拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.					DWGNO.	XXXX			
					2				
					1				



拓宜(上海)工控电器设备有限公司
Topone (Shanghai) Industrial Control Electrical Equipment Co., LTD.