





2		1	
REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.21

Electrical :

	UL	IEC
1.Rated Voltage :	300V	250V
2.Rated Current :	8A	7A
3.Torque Value :	M2 , 1.77Lb.in	M2, 0.2N.m
4.Wire Range:	28-16AWG	0.5-1.5mm ²
5.Stripping Length :	6-7mm	
6.Withstanding Voltage :	AC1600V/1Min.	
7.Operating Temperature :	-40°C~+105°C	
8.RoHS Compliance		
9." ★ " is the key quality control point		



SECTION A-A



15ETYKM	- 3.5	- XXP	- X	X	- XX
①	②	③	④	⑤	⑥
① Series No.	② Pitch	③ Poles	④ 1 Single Pitch 2 Double Pitch	⑤ Color: 1 Grey 2 Blue 3 Black 4 Green 5 Orange 6 Red 7 Transparent 8 Yellow 9 White	⑥ Customer Request : 00--Standard
02 02Contacts		03 03Contacts			
24 24Contacts					

6	SCREW-02	XX	2	Steel	Zn Plated				
5	SCREW-01	XX	P	Steel	Zn Plated				
4	BLOCK	XX	P	Brass	Ni Plated				
3	CLAMP	XX	P	Phosphor Bronze	Ni Plated				
2	COVER	XX	1	PA66(UL94V-0)	SEE NOTE				
1	HOUSING	XX	1	PA66(UL94V-0)	SEE NOTE				
ITEM	NAME OF PART		NO. OF PART		Q"TY	MATERIAL		NOTE	
DWG.	YL	DATE	22.11.21		SIZE	A4	UNITS	mm	SHEET/OF 1 / 1
CHK.		DATE			SCALE	1:1			
APP.		DATE			NAME	15ETYKM-3.5-XXP-XX-00			
 拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.									
				DWGNO.	XXXX				



拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

A	Total Pitch Tolerances in mm									Nominal dimension range in mm									$\perp$		$\equiv$	$-$	$//$						
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150				
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10	to all	to 100	to 150	to 100	to 150	to 150				
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3	0.3	0.2	0.3	0.5					
6										5										4									