




目录 MAPX	设变内容 MODIFICATION	日期 DATE

规格说明: Specifications:
电气特性: Electrical:
1. 额定电流: Current Rating
1A/contact terminalg
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding
Voitage
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance
1000MEGA ohms MIN
物理性能: Mechanical:
1. 插拔力: Cnnector Mate and Unmate Force
Mate force: 35N (MAX)
Unmate force: 7N (MIN)
材料: Matorial:
1. 塑胶: Housing:
PBT
2. 端子: Contact:
Copper Alloy C2680
3. 外壳: Shell:
SPCC
电镀Finish:
1. 端子: Contact:
Plated Gold in Mating Area,
Tin On Solder Talls
2. 外壳: Shell
Nickel Plating
温度范围: Temperature Range:
-30 C to +80 C

PCB LAYOUT

产品图 PRODUCT CHART DWG				深圳市韩下电子有限公司				
公差表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	黄彬	客户料号 PRODUCT PART NO.
X.	±0.30	X'.	±6'	比例 SCALE	1:1	审核 CHKD	张伟	产品名称 PRODUCT NO.
.X	±0.25	.X'	±3'	日期 DATE	2014/04/23	核准 APPD	罗小春	角法 VIEW
.XX	±0.20	.XX'	±2'	HX AF 90 ° WJDG ZB				
未标注的公差按一般标准计算				版本 VER				
				A0				