



Description:

This N-Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.

Features:

- 1) $V_{DS}=60V, I_D=10A, R_{DS(on)} < 18m\Omega @ V_{GS}=10V$ (typ: $15.5m\Omega$)
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 5) Excellent package for good heat dissipation.
- 6) MSL3



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
DO4266	4266	SOP-8	3000 pcs/Reel

Absolute Maximum Ratings: ($T_A=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current	10	A
	Continuous Drain Current- $T_A=100^\circ\text{C}$	6.5	
I_{DM}	Pulsed Drain Current ¹	40	
P_D	Power Dissipation	1.64	W
E_{AS}	Single pulse avalanche energy ²	72	mJ
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55-+150	$^\circ\text{C}$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	76	$^\circ\text{C}/\text{W}$

Electrical Characteristics: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourtce Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	60	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =60V	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 20V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	Gate-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	1	1.5	2.5	V
R _{DS(ON)}	Drain-Source On Resistance ³	V _{GS} =10V, I _D =10A	---	15.5	18	m Ω
		V _{GS} =4.5V, I _D =5A	---	18	23	m Ω
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =25V, V _{GS} =0V, f=1MHz	---	1890	---	pF
C _{oss}	Output Capacitance		---	141	--	
C _{rss}	Reverse Transfer Capacitance		---	120	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DS} =30V, I _D =5A, R _{ENG} =1.8 Ω ,V _{GS} =10V	---	9.4	---	ns
t _r	Rise Time		---	15.7	---	ns
t _{d(off)}	Turn-Off Delay Time		---	37.8	---	ns
t _f	Fall Time		---	6.3	---	ns
Q _g	Total Gate Charge	V _{GS} =10V, V _{DS} =30V, I _D =5A	---	48	---	nC
Q _{gs}	Gate-Source Charge		---	7.3	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	10.5	---	nC
Drain-Source Diode Characteristics						
V _{SD}	Diode Forward Voltage	V _{GS} =0V, I _{SD} =10A	---	---	1.2	V
I _S	Continuous Drain Curren	V _D =V _G =0V	---	---	10	A
I _{SM}	Pulsed Drain Current		---	---	40	A

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition : $T_J=25^{\circ}\text{C}, V_{DD}=30V, V_G=10V, L=0.5mH$
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$

Test Circuit




Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveform




Figure 3: Unclamped Inductive Switching Test Circuit & Waveform





Figure 4: Diode Recovery Test Circuit & Waveform



SOP-8 Package Information:


COMMON DIMENSIONS			
CUNITS MEASURE=MILLIMETER			
SYMBOL	MIN	NOM	MAX
A	1.350	—	1.750
A1	0.100	—	0.250
A2	1.350	—	1.550
b	0.330	—	0.510
c	0.170	—	0.250
D	4.700	—	5.100
E	3.800	3.900	4.000
E1	5.800	—	6.200
e	1.270BSC		
L	0.400	—	1.270
θ	0°	—	8°

Unit:mm

Tape & Reel Information

Dimensions in mm



Marking Information:


①. Part NO.

②. Date Code(YWWG / R)

Y : Year Code , last digit of the year

WW : Week Code(01-53)

G/R : G(Green) /R(Lead Free)



Previous Version

Version	Date	Subjects (major changes since last revision)
2.0	2024-04-29	Release of final version

Attention :

- Information furnished in this document is believed to be accurate and reliable. However, Shenzhen Doingter Semiconductor Co.,Ltd. assumes no responsibility for the consequences of use without consideration for such information nor use beyond it.
- Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Shenzhen Doingter complies with the agreement. Products and information provided in this document have no infringement of patents.
- Shenzhen Doingter assumes no responsibility for any infringement of other rights of third parties which may result from the use of such products and information. This document supersedes and replaces all information previously supplied.



Is

a registered trademark of Shenzhen Doingter Semiconductor Co., Ltd. Copyright © 2013

Shenzhen Doingter Semiconductor Co.,Ltd. Printed All rights reserved.