









10~15P




P.C.B LAYOUT
TOLERANCE:±0.05




5P~6P




7P~9P



2P



3P



4P

Ordering Information:
A2012WR-S-XP - ***

1 2

1.Part NO.

2.Material:

(Blank):Nylon 6T,UL94V-0

GWT:Nylon 6T,UL94V-0,GWT 750℃

SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40℃ ~ +105℃

Contact Resistance: 20mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 800V AC/minute

Pin Material:Brass/Tin over Nickel

Material:Nylon 6T,UL94V-0(Ivory)

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.00	8.00	4.50	9P	16.00	22.00	18.50
3P	4.00	10.00	6.50	10P	18.00	24.00	20.50
4P	6.00	12.00	8.50	11P	20.00	26.00	22.50
5P	8.00	14.00	10.50	12P	22.00	28.00	24.50
6P	10.00	16.00	12.50	13P	24.00	30.00	26.50
7P	12.00	18.00	14.50	14P	26.00	32.00	28.50
8P	14.00	20.00	16.50	15P	28.00	34.00	30.50

CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE	
mm	3:1	1 of 1		
DRAWN	CHK'D	APPR		
Chengbiao Ye	Diankui Wan	Jack Yin	2.00mm Pitch Right angle Wafer - SMT Type	
General Tolerances		THIRD ANGLE PROJECTION	DRAWING NO.	
x,xx±0.25 x,xx±0.20 x,xxx±0.15 ANGLES ±1°				
			REV A4	
A2012WR-S-XP				