




REV.	ECN NO.	REVISED	DATE



NOTE:

1.MATERIAL:

a.HOUSING:LCP UL 94V-0 BLACK

b.CONTACTS:C5191

(SURFACE PLATING: Ni for SALT TEST 48H)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 100 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BS-02-A4BJ006-48H

电池座系列

BS-02系列

DIP 90° TYPE

PLATING:

A-Au

J-Ni

K-Sn

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK

工程部

2024-11-14

LQ. HAUNG

PCB Layout Diagram
Top View

3	TERMINAL(-)	1	C5191 T=0.20MM	Ni-Plating for SALT TEST 48H
2	TERMINAL(+)	1	C5191 T=0.40MM	Ni-Plating for SALT TEST 48H
1	HOUSING	1	LCP UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2024-11-14	TITLE:	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-11-14	BS-2032-2-1 2.0 LCP Ni DIP 盐雾48H	
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2024-11-14	PART NO.:	
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW: ④ ⑤	BS-02-A4BJ006-48H	
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY	DRAW NO.:MY-CP-0448	