









RoHs


VER	MARK	PR. BY	DESCRIPTION	DATE



PIN	MODLE
Ø 2.0	DC025M-A20
Ø 2.5	DC025M-A25



SCHEMATIC



PCB. WELDING DRAWING

Main technical performance

Rated electrical load	DC 24V 2.5A
Contact resistance	≤0.03 Ω
Insulation resistance	≥100M Ω
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20C° ~+70C°
service life	5000cycles

GENERAL TOLERANCES
UNLESS SPECIFIED

X.* ±0.30	X.* ±5°
X.X* ±0.25	X.X* ±1°
X.XX*±0.15	

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
DC025M-AN

DESIGN: James
CHED: Talen
APPD: Sophia

TITLE:
DC SOCKET

CUSTOMER	SIZE A4	UNITS MM
	SCALE N:A	SHEET 1/1