






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14NOV22	B.D	J.Z
	A1	ECN-23-192938	06JAN23	B.D	J.Z
	A2	ECN-24-271512	21JUN24	GSK	J.Z



NOTES: A2

1) FOR COUNTERPART DETAILS, SEE SHEET 2 OF 2

2) TE CONNECTIVITY TRADE MARK, (IN ALTERNATIVE: "AMP" LOGO, OR "Tyco Electronics" LOGO)

3) SEALING (COLOUR YELLOW FOR LSR VERSION) (COLOUR WHITE FOR FSL VERSION)

4) DATECODE (OPTIONAL IN OLD MOULDS).

5) MOULD/MOULD CAVITY NUMBER

HSG-BROWN, SL-RED	HOUSING+SEC. LOCK: PA66-GF SEALING: LSR	2435050-4
HSG-GREEN, SL-RED		2435050-3
HSG-GRAY, SL-RED		2435050-2
HSG-BLACK, SL-RED		2435050-1
FINISH/COLOR	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. DONG 14NOV2022	TE Connectivity		
		CHK S. FAN 14NOV2022			
		APVD J. ZONG 14NOV2022	NAME		
		PRODUCT SPEC 108-20090	AMP SUPERSEAL 1.5 SRS. 2 POSITIONS PLUG ASS'Y		
		APPLICATION SPEC 412-20000			
		WEIGHT 2.60gr	SIZE A3	CAGE CODE 00779	DRAWING NO C-2435050
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 2	REV A2



DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ±0.3	±0.3
		1 PLC ±0.3	±0.3
		2 PLC ±0.3	±0.3
		3 PLC ±0.3	±0.3
		4 PLC ±0.3	±0.3
		ANGLES ±2°	±2°
MATERIAL -		FINISH -	-
SEE TABLE		SEE TABLE	SEE TABLE

PRE-ASSEMBLED SECONDARY LOCK (COLOUR RED/WHITE)


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

COUNTERPART DETAILS


SECTION A - A




TAB DETAILS



SECTION C - C



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. DONG	14NOV2022	 TE Connectivity	
		CHK S. FAN	14NOV2022		
		APVD J. ZONG	14NOV2022		
		PRODUCT SPEC 108-20090			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP SUPERSEAL 1.5 SRS. 2 POSITIONS PLUG ASS'Y	
		0 PLC ±0.3		SIZE	
		1 PLC ±0.1		CAGE CODE	
		2 PLC ±0.05		DRAWING NO	
		3 PLC ±		RESTRICTED TO	
		4 PLC ±		-	
		ANGLES ±2°		A300779C-2435050	
MATERIAL		FINISH		SCALE 2:1	
				SHEET 2 OF 2	
CUSTOMER DRAWING		WEIGHT 2.60gr		REV A2	