




Wire Wound Type Common Mode Filter


- 1.High common mode impedance at high frequency cause excellent noise suppression performance.
- 2.ACM2012-2P series realizes small size and low profile. 2.0x1.2x1.2 mm.
- 3.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 4.Operating Temperature Range: -40 °C to +85 °C.

Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
ACM2012-2P-102TF H	750~1000	100	0.88	300	50	125	10M

MECHANICAL




SUGGEST LAYOUT




Dimension : mm


SCHEMATICS



IMPEDEANCE FREQUENCY




TAPING AND PACKING



Direction of unreeling

IND1752-J-E

Reel



Dimensions in mm

Quantity (pcs):
2000 PCS PER REEL
5 REELS PER CARTON
10000PCS PER CARTON

Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
Tel:0755-27652992 29016433 E-mail: sales1@cd-tek.com Website:www.cd-tek.com