

■ Features

- SMD construction, and low profile.
- High Impedance and Excellent Frequency Characteristic.
- Self Electromagnetic Shielding.
- Low Magnetic Flux Leakage.

■ Applications

- LED Light, TV game, Monitor, etc.
- EMI common-mode noise.

■ Product Identification

<u>YLM</u>	<u>□□□□</u>	<u>—□□□</u>	<u>T</u>
(1)	(2)	(3)	(4)


(1) : Type

(2) : Dimensions

(3) : Impedance


(4) : Taping

■ Shapes and Dimensions (Unit: mm)



TYPE	A	B	C	D Typ	E Typ	F Typ
YLM1008	10.00±0.30	8.00±0.30	5.00±0.30	2.55	2.00	0.60

■ Circuit Diagram




■ YLM1008 Series

Part Number	Z (Ω) @100MHz/0.1V	RDC (mΩ) Max.	Rated Current (A) max.	Rated Volt. (V)max.	IR(MΩ) min.	Marking
	Typ					
YLM1008-470T	300	90	3.5	50	10	无
YLM1008-401T	400	6.5	7.0	50	10	401
YLM1008-751T	750	10	5.0	50	10	751
YLM1008-861T	860	45	5.0	50	8	861
YLM1008-102T	1000	15	10.0	50	10	无

Material List

NO.	ITEM	DESCRIPTION	SUPPLIER
1	CORE	FERRITE	SINCORES OR EQ
2	WIRE	2UEW P180	PACIFIC OR EQ
4	SOLDER	Sn Cu	SHENYUAN OR EQ
5	EPOXY	661	QIFU OR EQ
6	INK	Black	BON MARK


Reliability Testing

Operating Temperature	- 40 to + 125 °C (Contain Heating coil)
Appearance Inspection	No external defects by visual inspection
Terminal Strength 	After soldering , between copper plaet and terminals of coils , push in two directions of X , Y with standing 10N(1.02kg) for10+/-2 sec. Terminal should not peel off. (Refer to figure at right)
Heat endurance of reflow soldering	Refer to figure
Insulating resistance	Over 100 MΩ at 100V D.C . between wire and core .
Dielectric Strength	Apply at 0.5KV 3mA for 1 minute between wire and core .
Temperature characteristics	Inductance coefficient (0~2,000) × 10 / °C (- 30 ~ + 100 °C)
Humidity characteristics	Inductance deviation within ± 10% , after 96 hours in 90~95% relative humidity at 40 ± 2 °C and 1 hours drying under normal condition .
A test is made under the above mentioned condition , and it is kept for 2 hours in the normal	

■ Recommended soldering temp.Graph


IR Reflowprofile

Temperature℃




Temperature and humidity . After that , no mechanical and electrical defect should be found .

■ Taping Dimensions(Unit:mm)




TYPE	W	A	B	D	P	K	T	MPQ
YLM1008	24.0±0.3	7.6±0.1	9.6±0.1	7.5±0.1	16.0±0.1	5.1±0.1	0.35±0.05	500


■ Reel Dimensions(Unit:mm)



TYPE	W	W1	A	B	C	D
YLM1008	330±2.0	16.4±2.0	13.0±0.50	21.0±0.80	2.0±0.50	100Min

■ Direction of rolling



■ Cover tape peel off condition

Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed 300 ± 10 mm/min.