











NOTE:
 1.Material:
 HOUSING: HIGH TEMPERATURE LCP,BLACK,UL 94 V-0 FLAME RETARDANT.
 2.TERMINAL:NICKEL COPPER ALLOY
 3.CONTACT AREA PLATE NICKEL 50μ" MIN,PLATE GOLD 15μ" MIN SOLDER AREA PLATE NICKEL 50μ" MIN,PLATE MATT TIN 60-180μ"
 4.ELECTRICAL CHARACTERISTICS
 CONTACT CURRENT RATING :0.5AMPERE
 VOLTAGE RATING 30VAC
 CONTACT RESISTACE:50 MILLOHMS MAX
 DIELECTRIC WITHSTANDING VOLTAGE:300VDC
 5.ENVIRONMEENT
 OPERATION TEMPERATURE:-40°C TO 85°C

TITLE QSFP28 1X1 CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. QSFP28 2170704-8			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET: 1/3
			.XXX±0.10		REV:A



TITLE QSFP28 1X1 CONNECTOR			 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. QSFP28 2170704-8			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET: 2/3	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				



NOTES:

- DATUM G- DEFINED BY CENTERLINE OF PADDLE CARD WIDTH
- DATUM H- DEFINED BY LEADING EDGE OUTER MOST OF THIRD MATE CONTACTS (PADS)
-TO BE RE-ESTABLISHED ON EACH SIDE
- DATUM J- DEFINED BY TOP SURFACE OF PADDLE CARD
NO SOLDER MASK WITHIN 0.05 OF ALL DEFINED CONTACT PAD EDGES
NO SOLDER MASK BETWEEN END END CONTACTS AND THE SIDE EDGES OF THE PADDLE CARD

TITLE QSFP28 1X1 CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. QSFP28 2170704-8			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET: 3/3
			.XXX±0.10		REV:A