



**RoHS**

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		Jack	Larry	J.L.Y	2025-05-14

## NOTES:

1.ELECTRONIC:  
CONTACT RESISTANCE: 30mohm MAX  
INSULATION RESISTANCE: 100 Mohm MIN  
WITHSTAND VOLTAGE:AC 500V,1min.






## 2.MECHANICAL:

DURABILITY: 10000 CYCLE.

## 3.ENVIRONMENT CHARACTERISTICS:

OPERATING TEMPERATURE: -55°C TO +105°C

4.RECOMMANDER PCB THICKNESS 1.00MM



CF-043-T171B X

X

XXX

WR

## 外壳材质

S: 铁材

T: 不锈钢

C: 铜壳

E: 无外壳

## 外壳镀要求

E: 外壳镀镍

G: 外壳镀金

N: 无外壳

A: 外壳镀金 0.8u"

B: 外壳镀金 3u"

C: 外壳镀金 0.6u"

D: 外壳镀雾锡

F: 外壳镀金 1u"

## 产品盐雾要求

12H: 盐雾 12H

24H: 盐雾 24H

48H: 盐雾 48H

72H: 盐雾 72H

如无盐雾要求则不需标示

No.	PART NAME	QTY	MATERIAL	REMARK
3	SHELL	1	C2680-H T=0.35	AU PLATED
2	CONTACT	19	COPPER ALLOY T=0.15	AU PLATED
1	HOUSING	1	THERMOPLASTIC(LCP)	(UL 94V-0) BLACK

## TOLERANCES UNLESS OTHERWISE SPECIFIED

UNIT (MM)  
X. ±0.55  
X.X ±0.35  
X.XXX ±0.25  
X.XXX ±0.15  
ANGEL ±2°

ORIGINAL DATA  
2025-05-14  
DWG.  
Jack  
3RD.ANGLE'S  
CKD.  
Larry  
APPD.  
J.L.Y




东莞市辉煌精密有限公司

TITLE  
HD CF SMT H3.25 不锈钢镀镍


PART NO. HDMI-CF043-H3.25	SCALE 1:1	SIZE A4
DWG NO. HDMI-CF043-H3.25	SHEET 1/2	REV. A

RoHS

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		Jack	Larry	J.L.Y	2025-05-14



盘/每箱	PCS/每盘	PCS/每箱
10盘/每箱	1KPCS/每盘	10KPCS/每箱



TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉焕精密有限公司		
UNIT (MM)		ORIGINAL DATA 2025-05-14		TITLE HDMI C FEMALE SMT H3.25 无Logo 包装规范
X. ±0.55		DWG. Jack		
X.X ±0.35		CKD. Larry		PART NO. HDMI-FC043-H3.25
X.XX ±0.25		APPD. J.L.Y		SCALE 1:1 SIZE A4
X.XXX ±0.15		DWG NO. HDMI-FC043-H3.25		SHEET 2/2 REV. A
ANGEL ±2°				
3RD. ANGLE'S				