



SL310

3.0 AMP SCHOTTKY BARRIER RECTIFIERS



## FEATURES

- \* Ideal for surface mount applications
- \* Easy pick and place
- \* Built-in strain relief
- \* Low forward voltage drop

## MECHANICAL DATA

- \* Case: Molded plastic
- \* Epoxy: UL 94V-0 rate flame retardant
- \* Metallurgically bonded construction
- \* Polarity: Color band denotes cathode end
- \* Mounting position: Any
- \* Weight: 0.093 grams


## VOLTAGE RANGE

100 Volts

## CURRENT

3.0 Amperes

DO-214AA(SMB)



Dimensions in inches and (millimeters)

## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25 °C ambient temperature unless otherwise specified.

Single phase half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

TYPE NUMBER	SL310	UNITS
Maximum Recurrent Peak Reverse Voltage	100	V
Maximum RMS Voltage	70	V
Maximum DC Blocking Voltage	100	V
Maximum Average Forward Rectified Current		
See Fig. 1	3.0	A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	80	A
Maximum Instantaneous Forward Voltage at 3.0A	0.67	V
Maximum DC Reverse Current Ta=25°C	100	µA
at Rated DC Blocking Voltage Ta=125°C	20	mA
Typical Junction Capacitance (Note1)	240	pF
Typical Thermal Resistance R JA (Note 2)	70	°C/W
Operating Temperature Range T <sub>j</sub>	—	°C
Storage Temperature Range T <sub>stg</sub>	-55 to +150	°C

### NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
2. P.C.B. mounted with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

## RATING AND CHARACTERISTIC CURVES(SL310)

FIG.1-FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4-TYPICAL REVERSE CHARACTERISTICS




FIG.5-TYPICAL JUNCTION CAPACITANCE

