

RoHS

SPECIFICATIONS


Rated Current:1.5AMP

Contact Resistance: 20mΩ Max


Withstand Voltage:500V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)




Contact Material:Brass

Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max. Processing Temp: 230°C for 30–60 seconds
(260°C for 5 seconds)



Dimension antitheses list				
ITEM	PC	PB	PA	L
Alternate	3.00	17.50	4.70	25.20

深圳市连盛精密连接器有限公司

深圳市连盛精密连接器有限公司									
PART NO.		1010200227							
TITLE:		2.0PH 6H=6X2.0 2*3P DIP PA4.7 PB17.5 PC3.0 L=25.2 AU0.8U PA6T							
PROJ.		SCALE	FIT	UNIT	SIZE	SHEET	1/1	PROJ.	
DRAW				CHECK					
X.X				±0.30					
X.XX				±0.20					
X.XXX				±0.10					
Angle				±3°					
APPROVE									
CHANGE									
MODIFICATION DESCRIPTION									
DATE									
REV									