


1 Product Identification

GDNR 201610 - 1R0 M T F
① ② ③ ④ ⑤ ⑥


- ① Product Symbol
- ② Dimensions (See two)
- ③ Inductance Value (1R0:1.0μH)
- ④ Inductance Tolerance (J:±5%;K:±10%; M:±20%; N:±30%)
- ⑤ Packaging Style (B: Bulk; T: Tape & Reel)
- ⑥ Lead Free

2 Appearance, Dimensions(mm)



A	B	C	D	E
2.00±0.20	1.60±0.20	1.05Max.	0.80±0.2	0.60±0.2

LAND PATTERN DIMENSIONS



/	mm
f	0.7
g	2.2
h	1.6



3 Specifications


Part No.	Inductance L0(uH) $\pm 20\%$ @100KHz/1V	RDC (m Ω)Max	Saturation Current (A)Max	Heat Rating Current (A)Max
GDNR201610-1R0MTF	1.0	120	1.5	1.65
GDNR201610-2R2MTF	2.2	180	1.0	1.2

※ Note


*Rated current is the DC current that reduces the initial inductance by 30% or when the temperature rises $\Delta T = 40^{\circ}\text{C}$

4 Packaging

(1) Dimensions of Reel (mm)



(2) Dimensions of Tape (mm):



W	A0	B0	K0	P	F	E	D	P0	P2	T	Packaging quantity
8.0 ±0.3	1.86 ±0.1	2.2 ±0.1	1.2 ±0.1	4.0 ±0.1	3.5 ±0.1	1.75 ±0.1	1.55+ 0.1/-0.0	4.0 ±0.1	2.0 ±0.1	0.22 ±0.05	2000PCS/REEL