

**POLYMER PTC
RESETTABLE FUSE**




电路保护元器件专业制造商
Part Number: TLC-TRM075

1. Physical Dimensions

Unit:mm

P/N	A	B	C	D	E	Lead
	Max.	Max.	TYP.	Nor.	Max.	Φ
TRM075	15.4	23.9	5.1	10±2	4.0	0.80



2. Electrical Characteristics


P/N	I _H	I _T	V _{max} OP V _{ac}	I _{max}	V _{max} Interrupt V _{rms}	T _{trip} (Max time to trip)		P _{dtyp}	R _{min}	R _{max}	R1 _{max}
	(A)	(A)	(V)	(A)	(V)	Current(A)	time(S)	(W)	(Ω)	(Ω)	(Ω)
TRM075	0.75	1.50	240	7.5	265	3.75	18.0	2.6	0.32	0.62	0.99

- I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.
- I_T: Tripping Current minimum current at which the device will trip in 25°C still air.
- V_{max}: Maximum voltage device can withstand without damage at rated current.
- I_{max}: Maximum fault current device can withstand without damage at rated voltage.
- T_{trip}: Maximum time to trip(s) at assigned current.
- P_{dtyp}: Rated working power.
- R_{min}: Minimum resistance of device prior to trip at 25°C.
- R_{max}: Maximum resistance of device prior to trip at 25°C.
- R1_{max}: Maximum resistance of device is measured one hours post reflow at 25°C.

3. Thermal Derating (Maximum ambient operating temperature)

P/N	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
TRM075	1.19	1.04	0.89	0.75	0.60	0.53	0.45	0.38	0.29

4. Wave Soldering Parameters



5. Package Information

Packing quantity: 400pcs/bag

Tape and Reel Specifications:

Devices taped using EIA468-B/IEC286-2 standards.

Storage Condition: 0°C ~35°C, ≤70%RH, 2 Years

6. Agency Recognition: TUV



Caution: Operation beyond the rated voltage or current may result in rupture electrical arcing or flame. Specifications are subject to change without notice.

Web: www.tlcet.com.cn www.winvast.cn

TEL: 86-0769-3892 0554 FAX: 86-0769-8793 2077 E-mail: Tina@tlcet.com.cn

Address: No. 18, 5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710

Revision: E

Date: 2023-03-21

