



PC Board Layout

NOTES:

MATERIAL :

- |                    |                                  |
|--------------------|----------------------------------|
| 1.HOUSING MATERIAL | :GLASS FILLED POLYESTER UL94V-0. |
| 2.CONTACT MATERIAL | :PHOSPHOR BRONZE $\phi$ 0.45mm.  |
| 3.PLATING          | :GOLD PLATING OVER NICKEL.       |

ELECTRICAL:

- |                                      |                              |
|--------------------------------------|------------------------------|
| 1.VOLTAGE RATING                     | :125 VAC RMS.                |
| 2.CURRENT RATING                     | :1.5 AMP.                    |
| 3.CONTACT RESISTANCE                 | :30 MILLIOHMS MAX.           |
| 4.INSULATION RESISTANCE              | :500 MEGOHMS MIN @ 500V DC . |
| 5.DIELECTRIC WITHSTANDING RESISTANCE | :1000V AC RMS 50Hz. 1MIN.    |

MECHANICAL:

- |                            |                  |
|----------------------------|------------------|
| 1.DURRABILITY              | :750 CYCLES MIN. |
| 2.PCB RETENTION PRE-SOLDER | :1 LB MIN.       |

ENVIRONMENTAL:

- |              |             |
|--------------|-------------|
| 1. STORAGE   | : -40℃~+85℃ |
| 2. OPERATION | : -25℃~+85℃ |

TOLERANCE TABLE

|       |            |
|-------|------------|
| . 0   | $\pm 0.30$ |
| . 00  | $\pm 0.20$ |
| . 000 | $\pm 0.05$ |

|               |                     |                                                    |                 |       |        |
|---------------|---------------------|----------------------------------------------------|-----------------|-------|--------|
| APPROVED:     | DATE:               | C kmtw 深圳市灿科盟实业有限公司<br>CHANKEMENG INDUSTRYCO., LTD |                 |       |        |
| CHECKED:      | DATE:               | TITLE:<br>RJ11-6P/6C 8004 全塑 弯插 白色 上带缺口            |                 |       |        |
| DRAWN:<br>HCY | DATE:<br>2014-05-26 | PART. NO.                                          | R-RJ11R06P-A005 |       |        |
|               |                     | UNIT                                               | mm              | SCALE | free   |
|               |                     | FILE NO.                                           | Ckmtw-RJ11-0091 | REV.  | A HY04 |