


1

2


3

4


A



B





C



SCHEMATIC



AuGLAR	$\pm 5^\circ$
X.	$\pm 0.40$
X.x	$\pm 0.30$
X.xx	$\pm 0.20$
X.xxx	$\pm 0.15$
UNSPECIFIED	TOLERANCES
AuGLAR	$\pm 5^\circ$



2

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.16	阿树

3



NOTE:  
Rating: DC 12V 50mA  
Operating Force: 200±100gf  
Lifetime: 10,000 Cycles

PART NO	L	foot
SK-3245S-L1-X	L1:2.00	A B
SK-3245S-L2-X	L2:2.50	A B
SK-3245S-L3-X	L3:3.00	A B
SK-3245S-L4-X	L4:4.00	A B

ITEM	PART NAME	QTY	MATERIAL	FINISHING
5	Terminal	6	Brass(0.30t)	ag Plated
4	Contact spring	1	Phosphor bronze	ag Plated
3	Base	1	PA46	Black
2	Cover	1	Sus	Natural
1	Keystake	1	PA46	Black
ITEM	PART NAME	QTY	MATERIAL	FINISHING

DESIGN	阿树	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SK-3245S-L4-A
APPROVED		SIZE: A4	DWG NO.: X-SK-3245S-L4-A
		SCALE	1/1
		PAGE	A1
		REVISION	
		N/A	



1

2

3

4

A

B

C

D