



1 2 3 4 5 6 7 8 9


G




F



E



D



C

## SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$ , Min  
 Contact Resistance: 20m $\Omega$ , Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30–60 seconds  
 (260° C for 5 seconds)



® 深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X.X : ±0.25 X.X° : ±1°

X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME: HX IDC200-2-03-W-5.7

| SIZE | A4 | SCALE | N:1 | PROJECT NO. |
|------|----|-------|-----|-------------|
|------|----|-------|-----|-------------|

| REV | A | UNIT | mm | PROJECT |
|-----|---|------|----|---------|
|-----|---|------|----|---------|

| PAGE | 1/1 |
|------|-----|
|------|-----|

| DRAWN : | 黄彬 | 2020.6.24 | CHECKED: | 张伟 | 2020.6.24 | APPROVED: | 罗小春 | 2020.6.24 |
|---------|----|-----------|----------|----|-----------|-----------|-----|-----------|
|---------|----|-----------|----------|----|-----------|-----------|-----|-----------|

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6      | 4.00   | 6.00   | 24     | 22.00  | 24.00  | 42     | 40.00  | 42.00  | 60     | 58.00  | 60.00  |
| 8      | 6.00   | 8.00   | 26     | 24.00  | 26.00  | 44     | 42.00  | 44.00  | 62     | 60.00  | 62.00  |
| 10     | 8.00   | 10.00  | 28     | 26.00  | 28.00  | 46     | 44.00  | 46.00  | 64     | 62.00  | 64.00  |
| 12     | 10.00  | 12.00  | 30     | 28.00  | 30.00  | 48     | 46.00  | 48.00  | 66     | 64.00  | 66.00  |
| 14     | 12.00  | 14.00  | 32     | 30.00  | 32.00  | 50     | 48.00  | 50.00  | 68     | 66.00  | 68.00  |
| 16     | 14.00  | 16.00  | 34     | 32.00  | 34.00  | 52     | 50.00  | 52.00  | 70     | 68.00  | 70.00  |
| 18     | 16.00  | 18.00  | 36     | 34.00  | 36.00  | 54     | 52.00  | 54.00  |        |        |        |
| 20     | 18.00  | 20.00  | 38     | 36.00  | 38.00  | 56     | 54.00  | 56.00  |        |        |        |
| 22     | 20.00  | 22.00  | 40     | 38.00  | 40.00  | 58     | 56.00  | 58.00  |        |        |        |

1

2

3

4

5

6

7

8

9

G

F

E

D

C

B

A