







NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 60 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VDC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : PBT UL94V-0./COLOR:BLACK
2. CONTACT MATERIAL : PHOSPHOR BRONZE Ø0.46mm
3. CONTACT PLATING : GOLD PLATING OVER NICKLE
4. SHIELD PLATING : NICKEL PLATING OVER BRASS
5. OPERATING LIFE : 750 CYCLES MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.

MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68, SUBPART F.

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称 TITLE	网络插座 (带灯带弹)	版本 REV.	A
			X. XX	±0.20	批 准				
			X. XXX	±0.10	APPROVAL				
			Angle	±3.0°	比 例	产品料号 PART NO.	HC-RJ45-059C-2x3-1	单位 UNITS	mm
序号	变更内容	日期			SCALE				
No.	MODIFY CONTENT	MODIFY DATE			投 影	材料		页 次	1/1
					Projection			SHEET	